

IW-HFM-4 – Interview Window 4-Button Master

Description

The **IW-HFM-4** is a flexible, hands-free intercom system specifically engineered for interview windows. When used properly, windows in close proximity will not experience feedback or crosstalk.

Features

- Hands-free communication
- Each Master selectively pages 2 zones plus an "All Call"
- Up to 6 paging zones per system
- LED indicates when paging system is in use
- Mounts on wall or desk with included hardware
- Music/program source can be integrated through paging interface box with no extra equipment
- Use optional RF headset or lapel mic for maximum comfort and mobility
- Separate junction box allows for easy installation



Specifications

Construction:	Stainless steel faceplate
Dimensions:	4.81(122) W x 8(203) H x 2.63(67) D in(mm)
Weight:	2.5 pounds (1.1 kg) (not including junction box)
Mounting:	Mount on desk with included stand or surface mount to wall
Communication:	Hands-free in both directions
Power Source:	Master and sub-station shipped with power supplies that convert 100-240VAC to 12VDC output (internationally accommodating male plugs included)
Wiring:	Factory wired cable from Master to remote; 2-pair paging bus
Lighting:	LED's indicate paging is in use and remote channel is active

Available Sub-Stations

Indoor Hands-Free Station:	Model IW-HFS-1 is an indoor, hands-free sub-station
Outdoor Hands-Free Station:	Model IW-HFS-2 is an outdoor, hands-free sub-station
Indoor Handset Station:	Model IW-HSS-1 is an indoor handset sub-station
Indoor Hands Free/Handset:	Model IW-HFS-1H is an indoor, hands-free sub-station with handset for privacy

Paging


Interface Box:	Model IW-IB-6 is used to control paging. One is needed per paging zone. Included power supply converts 100-220VAC to 12VDC output (internationally accommodating male plugs also included).
Ceiling Speaker:	Model S-8318B is an 8" indoor ceiling speaker with built in volume control
Horn Speaker:	Model K-C-20V is a horn speaker with built-in volume control

Other Accessories

Gooseneck Microphone:	Model IW-MIC is a gooseneck microphone for use with the IW Master
RF Headset/Mic:	Model HS-RF-1 is an RF Headset speaker and microphone (120V power supply standard. Order model K-VC-220 to operate on 220VAC, 50/60Hz)

IW-HFM-4 – Interview Window Master

Dimensions



Copyright 2010 Talk-A-Phone Co. All rights reserved.

Talk-A-Phone Co. • 7530 North Natchez Avenue • Niles, Illinois 60714-3804
Phone 773.539.1100 • Fax 773.539.1241 • info@talkaphone.com • www.talkaphone.com
All prices and specifications are subject to change without notice.
Talk-A-Phone, Talk-A-Lert, Scream Alert and WEBS are registered trademarks of Talk-A-Phone Co.