

ETP-WM-AED – Defibrillator Wall Mount Emergency Phone Station

Description

The **ETP-WM-AED** adds a controlled-access compartment that will fit virtually any AED (Automatic External Defibrillator) to the most robust and stylish wall mounted emergency phone station available.

The wall mount offers contemporary architectural styling and is constructed out of durable stainless steel. An always-lit LED Blue Light provides high visibility and gives passers-by a sense of security. Patrons can call emergency personnel with a simple push of a button. At the same time, the LED Blue Light begins to flash, attracting attention to the location. Authorized personnel answering the call can then remotely open the AED compartment. The Emergency Phone faceplate is illuminated at all times for clear visibility at night.

With the climate controlling options, the Defibrillator Emergency Phone Station provides outdoor access anywhere a life-saving AED may be needed.

Features

- Secured, recessed chamber to house AED unobtrusively
- Optional thermostatically controlled heater for AED compartment maintains temperature above freezing
- AED door can be either unlocked immediately at the initiation of a phone call or remotely by a guard as determined by the installer
- Attention-getting LED Blue Light is included and mounted inside a polycarbonate housing. The LED Blue Light is continuously lit and flashes for duration of a call when “EMERGENCY” button is pressed to draw attention to the unit.
- Emergency Phone is illuminated at all times by an LED Panel Light
- Vandal-resistant stainless steel construction
- Designed to resist extreme weather conditions
- A variety of signage, graphics and color choices are available
- ADA-compliant

Specifications

Dimensions (W x D x H):	10.7 x 8.2 x 45.1 in. (273 x 209 x 1146 mm)
Weight:	49 lbs. (22.2 kg)
Construction:	12GA (.105 in.) brushed stainless steel with impact-resistant polycarbonate lens and resistance to UV-fade
Colors:	Brushed stainless steel is standard. Available painted in custom colors.
Signage:	2 in. high reflective red “EMERGENCY” lettering with wide-angle visibility is standard. Available as “ASSISTANCE”, “INFORMATION”, or custom lettering, colors and graphics.
Lighting:	<div>LED Blue Light: 209 lumens peak, 78 flashes per minute, 70% of initial lumens after 50,000 hours of operation</div> <div>LED Panel Light: Ultra bright LEDs, 50,000 hour lifetime</div>
Power:	9.0 watts, 120VAC/12-24VDC/24VAC
Mounting:	Mounts to a wall or straps to a pole or a kiosk
Warranty:	2-year warranty



ETP-WM-AED – Defibrillator Wall Mount Emergency Phone Station

Options

ETP-WM-AED Configuration	Emergency Phone Options
Analog Connectivity	ETP-400 Series Phone
IP Connectivity	VOIP-500 Series Phone

ETP-WM-AED includes an LED Blue Light and LED Panel Light. Emergency Phone is purchased separately.

Accessories


Pole Mounting Kit:

Order **ETP-PMKT** Pole Mounting Kit for strapping ETP-WM-AED to a pole.

Strapping Tool:

Order **ETP-PMKT-TOOL** Strapping Tool for use with **ETP-PMKT** Pole Mounting Kit.

Dimensional Diagram



All dimensions are in inches and are provided for reference only.