

4x4 FiberRunner® System Spillouts

- Spill-overs allow safe transition from horizontal to vertical runs
- 2" (50.8mm) bend radius control
- Transition to channel, slotted channel, and corrugated loom tubing
- Spill-over junction fittings can be retro-fitted to existing horizontal runs



FRVT4X4



FTR4X4



FIDT4X4BL



FRHD4KT



TRC4HDBL



FRLPR42BL

Part Number	Part Description	Couplers Required	Std. Pkg. Qty.	Std. Ctn. Qty.
-------------	------------------	-------------------	----------------	----------------

4x4 QuikLock™ Vertical Tee

FRVT4X4YL	Attaches to 4x4 channel and/or fittings to create a 90° vertical drop from a horizontal run. Hinged door included. Accepts FTR4X4YL, FIDT4X4BL, S4X4YL6 or E4X4YL6 directly. Accepts optional snap-on cover FRHC4YL6 in conjunction with channel.	(2 pcs.) FRBC4X4YL	1	5
------------------	---	-----------------------	---	---

3-Sided Vertical Tee Trumpet Spillout

FTR4X4YL	Used to limit the bend radius of the cable to 2" (50.8mm) when exiting from a 4x4 or 6x4 FiberRunner® Vertical Tee and 4x4 Fiber-Duct™ Fittings.	—	1	5
-----------------	--	---	---	---

2-Port Spillout to 1.5" (38mm) Inside Diameter Corrugated Tubing

FIDT4X4BL	Used to route cable into one or two pieces of 1.5" (38mm) diameter split corrugated tubing. Used with FRVT6X4YL, FRVT4X4YL, or FVT4X4YL. Securely holds corrugated split tubing to ensure system integrity and easy access to add or remove cables. Black color only.	—	1	5
------------------	---	---	---	---

4x4 Hinged Duct Vertical Cable Manager Kit

FRHD4KTYL	Provides secure, accessible route for cables spilling out from vertical tee to rack mounted equipment. Kit includes 6' length of 4x4 capacity hinged duct, 6' length of 4x4 hinged duct cover, one end cap for 4x4 hinged duct, three FZBA1.5X4 adjustable "Z" brackets, an adapter fitting, six WR4-C wire retainers and all required mounting hardware. Attaches directly to 6x4 and 4x4 vertical tee exit or FRLPR64 low profile reducer.	—	1	—
------------------	--	---	---	---

4x4 Hinged Duct Bend Radius Control Trumpet

TRC4HDBL	Bend radius control trumpet for exiting at the sidewall of 4" wall heights of type H hinged cover wiring duct channels. Maintains 1" (25.4mm) bend radius control. Black color only.	—	1	—
-----------------	--	---	---	---

Low Profile Reducer 4x4 to 2x2 for Vertical Tee

FRLPR42BL	Assembled into the 6x4 vertical tee FRVT6X4YL or 4x4 vertical tee FRVT4X4YL with an audible snap, the FRLPR42BL allows for the transition to 2x2 FiberRunner® or 2x2 Fiber-Duct™ Channel with minimal space required. No tools required for assembly. Black color only.	—	1	5
------------------	---	---	---	---

For other colors replace suffix YL (Yellow) with OR (Orange) or BL (Black).

4x4 FiberRunner® System Spillouts (continued)



FRSPJ2X2



FRSPJC24



FTR2X2



FIDT2X2



FRHD2KT



TRC2HDBL



FRSPJ4X4

Part Number	Part Description	Couplers Required	Std. Pkg. Qty.	Std. Ctn. Qty.
Spill-Over Junction with 2x2 Exit				
FRSPJ2X2YL	Assembles onto 4x4, 6x4, 12x4, or 24x4 FiberRunner® Channel, spilling over the side into a 2x2 vertical exit. Requires coupler to attach 2x2 FiberRunner® and fittings to the vertical exit. Mounts directly to existing installation with no alteration required. Mounting hardware provided for secure attachment.	(1 pc.) FBC2X2YL	1	—
Cover for Spill-Over Junction with 2x2 Exit for 4x4 Channel				
FRSPJC24YL	Used to fully enclose 4x4 channel in conjunction with the spill-over junction FRSPJ2X2YL. Cover snaps onto the channel base. Hinged feature allows easy access to add or remove cables.	—	1	5
3-Sided BRC Trumpet Spillout for 2x2 Exit				
FTR2X2YL	Used to limit the bend radius of the cable to 2" (50.8mm) when exiting from a spill-over junction with a 2x2 exit or from 2x2 Fiber-Duct™ Channel. Securely holds split corrugated tubing to ensure system integrity and easy access to add or remove cables.	(1 pc.) FBC2X2YL	1	5
1-Port Spillout to 1.5" (38mm) Inside Diameter Corrugated Tubing				
FIDT2X2YL	Used to route cable into one piece of 1.5" (38mm) diameter split corrugated tubing. Used with a spill-over junction with a 2x2 exit, 2x2 Fiber-Duct™ Fittings, and the 2x2 FiberRunner® Hinged Channel. Securely holds split corrugated tubing to ensure system integrity and easy access to add or remove cables.	(1 pc.) FBC2X2YL	1	5
2x2 Hinged Duct Vertical Cable Manager Kit				
FRHD2KTYL	Provides secure, accessible route for cables spilling out from a vertical tee or spill-over junction to rack mounted equipment. Kit includes 6' length of 2x2 FiberRunner® Hinged Channel H2X2YL6, 6' length of 2x2 snap-on hinged cover HC2YL6, four adjustable "Z" brackets FZBA1.5X4, one FiberRunner® 2x2 End Cap FHDEC2X2YL, six hinged duct 2" wire retainers WR2H-C and all required mounting hardware. Attaches to 2x2 vertical tee exit or spill-over junction with a 2x2 exit with a 2x2 QuikLock™ Coupler FBC2X2YL. Also attaches directly to 4x4 or 6x4 vertical tee exits with low profile reducer FRLPR42BL.	—	1	—
2x2 FiberRunner® Bend Radius Control Trumpet				
TRC2HDBL	Bend radius control trumpet for exiting at the sidewall of 2" wall heights of type H hinged cover wiring duct channels. Maintains 1" (25.4mm) bend radius control. Black color only.	—	1	10
Spill-Over Junction with 4x4 Exit				
FRSPJ4X4YL	Assembles onto 4x4, 6x4, 12x4, or 24x4 FiberRunner® Channel, spilling over the side into a 4x4 vertical exit. Requires coupler to attach 4x4 FiberRunner® Channel and fittings to the vertical exit. Mounts directly to existing installation with no alteration required. Mounting hardware provided for secure attachment.	(1 pc.) FRBC4X4YL	1	—

For other colors replace suffix YL (Yellow) with OR (Orange) or BL (Black).

Table continued on page J.46

4x4 FiberRunner® System Spillouts (continued)



FRSPJC44



FRTR4X4



FRIDT4X4



FR1.5IDE



FRUPS4X4

Part Number	Part Description	Couplers Required	Std. Pkg. Qty.	Std. Ctn. Qty.
-------------	------------------	----------------------	----------------------	----------------------

Cover for Spill-Over Junction with 4x4 Exit for 4x4 Channel

FRSPJC44YL	Used to fully enclose 4x4 channel in conjunction with the spill-over junction FRSPJ4X4YL. Cover snaps onto the channel base. Hinged feature allows easy access to add or remove cables.	—	1	5
-------------------	---	---	---	---

3-Sided BRC Trumpet Spillout for 4x4 FiberRunner® Exit

FRTR4X4YL	Used to limit the bend radius of the cable to 2" (50.8mm) when exiting from 4x4 FiberRunner® Channel or a 4x4 FiberRunner® Horizontal Tee.	(1 pc.) FRBC4X4YL	1	5
------------------	--	----------------------	---	---

2-Port Spillout to 1.5" (38mm) Inside Diameter Corrugated Tubing

FRIDT4X4YL	Used to route cable into one or two pieces of 1.5" (38mm) diameter split corrugated tubing. Requires coupler to be used with 4x4 FiberRunner® Fitting. Used with any 4x4 FiberRunner® Fitting. Securely holds corrugated split tubing to ensure system integrity and easy access to add or remove cables.	(1 pc.) FRBC4X4YL	1	5
-------------------	---	----------------------	---	---

1-Port Spillout Side Exit to 1.5" (38mm) Inside Diameter Corrugated Tubing

FR1.5IDEYL	Used to route cable into 1.5" (38mm) diameter split corrugated tubing directly through a hole cut in the side wall of the 4x4, 6x4, and 12x4 FiberRunner® Channel or 4x4 Fiber-Duct™ Channel. Provides 1" (25.4mm) bend radius control at the exit. Securely holds split corrugated tubing to ensure system integrity and easy access to add or remove cables. Includes drilling template.	—	1	5
-------------------	--	---	---	---

4x4 Up Spout

FRUPS4X4YL	Allows cable to be directed upward out of the channel deployed directly below racks and cabinets in underfloor installations. Provides 2" (50.8mm) bend radius. Snaps directly onto the channel and can be positioned to allow cables to be laid in. A 1" (25.4mm) top bezel is included. Other fittings can be installed for specific applications including FTR4X4YL and FIDT4X4BL.	—	1	5
-------------------	---	---	---	---

For other colors replace suffix YL (Yellow) with OR (Orange) or BL (Black).