

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

COVER REMOVED FOR CLARITY

PAN-TY LOOPS  
FOR CABLE FOLD-DOWNS  
(3 PLACES)

BREAKOUT AREA  
(3 PLACES)

KNOCK OUT  
MOUNTING HOLES  
FOR #6 PAN  
HEAD SCREW  
(INCLUDED)

3.281  
[83.34]

POST FOR TAMPER  
RESISTANT SCREW

3.28  
[83.3]

.94  
[24.0]

4.65  
[118.1]

PANDUIT P/N

WEIGHT

CBXS4\*\*\*AY

1.07 LB/10 PCS  
1485.3 g/10 PCS

#### NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. SEE CATALOG FOR A COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. DIMENSIONS IN ( ) ARE IN METRIC.
4. BOX INCLUDES:
  - 1- BOX BASE
  - 1- BOX COVER
  - 2- PLT1,5: -M PAN-TY
  - 1- LABEL/ LABEL COVER
  - 2- MOUNTING SCREW
  - 1- MOUNTING SCREW (USED TO SECURE COVER TO BASE)
  - 2- STRIP OF 1.00" X .75" FOAM TAPE FOR MOUNTING
  - 1- STRIP OF 3.00" X .75" FOAM TAPE FOR MOUNTING
5. BASE HAS TWO POCKETS FOR OPTIONAL MAGNET (CSBM-X1)
6. BREAKOUTS DESIGNED TO ACCEPT LD3/LCP3 AND LD5/LCP5 RACEWAY.
7. BASE MATERIAL THICKNESS= .090( 2.29 ).

NO WARRANTY, EXPRESSED OR IMPLIED, IS MADE BY PANDUIT WITH RESPECT TO ADHESIVE BOND PERFORMANCE. AMONG OTHER THINGS, THE CONDITIONS UNDER WHICH THESE MOUNTS MAY BE APPLIED AND/OR THE SURFACE TO WHICH THEY MAY BE APPLIED ARE BEYOND PANDUIT'S CONTROL.

NETWORK SYSTEMS

JAN 25 1988

ENGINEERING DEPT

DRAWING FILE NAME

M02479EUL00127-000A.DPT

SIZE

A

MINI-COM 4 POSITION SHUTTERED  
SURFACE MOUNT BOX CUSTOMER DRAWING



**PANDUIT**™  
CORP.  
TINLEY PARK, ILL 60477



ALL DIMENSIONS ARE GIVEN IN INCHES,  
UNLESS OTHERWISE SPECIFIED.  
DIMENSIONAL TOLERANCES ARE:  
1.X1 ± .010 1.XXX1 ± .0010  
1.XXX1 ± .0010 ANGLES ± .010

QUANTITY

12-27-86

DATE

BOX: ABS  
DOORS: PC

1:1 NUMBER N/A

PRODUCT SPEC N/A

WORK INSTRUCTIONS N/A

SCALE NONE

PART NO. CBXS4\*\*\*AY

DRAWING NO. 02479-127

| REV | DATE     | BY  | CHK | DESCRIPTION            | ECN       | R | CUST | SUP | OTH |
|-----|----------|-----|-----|------------------------|-----------|---|------|-----|-----|
| 1   | 12-27-86 | JAP |     | RELEASED TO PRODUCTION | 02479-127 |   |      |     |     |