



Shown with optional accessories

FEATURES

- 19" EIA 310-D Compliant
- A feature-rich wall mount, offering many of the same options as a full-size enclosure
- 2 pair of #12-24 rails; fully adjustable
- Solid Steel or Plexiglas Doors
- 1, 2, 3, and 4" conduit knockouts on top and bottom of rear section; 1, 2, 3, and 4" on rear section
- Industrial grade hinges provide added strength for rear section
- Doors and sides fully gasketed
- Center swing-out section provides front/rear access to cables
- Solid and vented sides available
- Weight tested to 1/2" of deflection

WS SERIES PART NO.

GL24WS-SS	24"H x 24"W x 24"D, 11 RMU, Weight capacity 250 lbs.*, Shipping wt. 125 lbs., Solid Front Door & Solid Sides
GL24WS-SV	Same as GL24WS-SS except with Solid Front & Vented Sides
GL24WS-PS	Same as GL24WS-SS except with Plexi Front & Solid Sides
GL24WS-PV	Same as GL24WS-SS except with Plexi Front & Vented Sides
GL36WS-SS	36"H x 24"W x 24"D, 18 RMU, Weight capacity 300 lbs.*, Shipping wt. 150 lbs., Solid Front Door & Solid Sides
GL36WS-SV	Same as GL36WS-SS except with Solid Front & Vented Sides
GL36WS-PS	Same as GL36WS-SS except with Plexi Front & Solid Sides
GL36WS-PV	Same as GL36WS-SS except with Plexi Front & Vented Sides
GL48WS-SS	48"H x 24"W x 24"D, 25 RMU, Weight capacity 350 lbs.*, Shipping wt. 200 lbs., Solid Front Door & Solid Sides
GL48WS-SV	Same as GL48WS-SS except with Solid Front & Vented Sides
GL48WS-PS	Same as GL48WS-SS except with Plexi Front & Solid Sides
GL48WS-PV	Same as GL48WS-SS except with Plexi Front & Vented Sides

*All maximum weight capacities determined at minimal deflection.

ACCESSORIES PART NO.

7219	6 position Power Strip for 19" mounting; 5-15R receptacle and 5-15P plug
7219-SR14	14 position (6 front/8 back) Power Strip for 19" mounting; 5-15R receptacle and 5-15P plug with surge protector
7206-FR-A18	Stationary Shelf (front/rear mount adjustable), 17.5"W x 18"D, 150 lb. weight capacity
7206-SL	Sliding Shelf, 16.343"W x 17.5"D, 40 lb. weight capacity
CBB-19	Copper Bus Bar for 19" mounting (isolated)
GR102	Grounding Kit for use with WM, WD, WS, and WE Wall Mounts
7217WS	Fan Assembly with Fan Guards and two 75 CFM fans
FFK1	Four Fan Filters
WS-22	66/110 Block Mounting Panel
7208WS	One Set of 5 Casters, 2 locking and 3 non-locking