

product spotlight

NEMA 12 WALL MOUNT ENCLOSURE

NEMA Type 12 Enclosures are constructed for indoor use to provide a degree of protection to personnel against access to hazardous parts; protection to equipment inside the enclosure against ingress of solid foreign objects (falling dirt and circulating dust, lint, and fibers); and protection with respect to harmful effects on the equipment due to the ingress of water (dripping and light splashing).

Features

- 19" EIA 310-D Compliant
- Two pair of 12 gauge, #12-24 threaded mounting rails, adjustable front to back
- Reversible mounting
- Keyed locks with dust covers
- Front and rear sections lock independently
- Provisions for cable access for 1", 2", and 3" conduit knock-outs
- 14 gauge main body in rear section



Available in black only

Part No.

GL240N12

Description

24.00"H x 24.00"W x 24.00"D,
Rack Space 12 RMU, Wt. cap. 150 lbs.,
Shipping wt. 105 lbs.; can accept one
FFKN12-A4

GL360N12

36.00"H x 24.00"W x 24.00"D,
Rack Space 19 RMU, Wt. cap. 250 lbs.,
Shipping wt. 140 lbs.; can accept two
FFKN12-A4


GL480N12

48.00"H x 24.00"W x 24.00"D,
Rack Space 26 RMU, Wt. cap. 300 lbs.,
Shipping wt. 175 lbs.; can accept three
FFKN12-A4

GREAT LAKES CASE & CABINET



Invest in Solid Engineering



CORPORATE HEADQUARTERS

P.O. Box 551
Edinboro, PA 16412
1.866.TRY.GLCC
(1.866.879.4522)
Phone: 814.734.7303
Fax: 814.734.3907
glcc@greatcabinets.com

GREAT LAKES MANUFACTURING, INC.

1521 Enterprise Road
Corry, PA 16407
Phone: 814.734.2436
Fax: 814.665.7025
werackyourworld.com
glm@greatmanufacturing.net

WESTERN DISTRIBUTION

4750 Joule Street
Reno, NV 89502
Phone: 775.829.9913
Fax: 775.829.9926
glcc@greatcabinets.com

GREAT LAKES INTERNATIONAL LTD.

Aerbridge House, Unit 14
Dunshaughlin Business Park
Dunshaughlin Co. Meath
Ireland
Phone: 011 353 1 825 8777
Fax: 011 353 1 825 8778

GREAT LAKES HUNGARY KFT

Zsurló utca 13
8000 Székesfehérvár
Hungary
Phone: 011 36 22 880 420
Fax: 011 36 22 880 429