



431 Aluminium Foil Tape

(No. 439 Lined Version)

Product Data Sheet

Updated : March 1996
Supersedes : October 1993

Product Description An aluminium foil with transparent acrylic adhesive designed for permanent sealing, holding, splicing or masking requiring the protection offered by a foil backing.

Physical Properties
Not for specification purposes

Adhesive Type	Acrylic	
Backing	Aluminium foil	
Thickness (ASTM D-3652)	90 µm	
Backing Thickness	50 µm	
Tape Colour	Shiny silver	
Shelf Life	12 months from date of despatch by 3M when stored in the original carton at 21°C (70°F) & 50 % Relative Humidity	

Performance Characteristics
Not for specification purposes

Adhesion to Stainless Steel ASTM D-3330	4.4 N/10mm	
Tensile Strength ASTM D-3759	3.0 N/10mm	
Elongation at Break ASTM D-3759	5.0 %	
Temperature Range Maximum	150 °C	
Water Vapour Transmission Rate	.1.55g water/m ² / 24h	

Date : March 1996
431 Aluminium Foil Tape

Additional Product Information	Foil backing provides an excellent reflective surface for both heat and light.	Good, long ageing performance both indoors and out.	Low moisture vapour transmission rate offers excellent sealing and patching performance.
Application Techniques	Best results are attained when applied to a clean, dry and non dusty surface above 0°C.	To improve adhesion ensure firm an even application pressure is applied.	
Applications	Seal and patch tears in truck trailers, as well as other equipment tested outdoors.	Heat reflection and cold conduction in appliances. Mechanical holding and splicing in general industry.	Good maskant in electroplating of aluminium, as well as other critical operations.
	FEATURES	ADVANTAGES	BENEFITS
	Aluminium foil backing.	Ultimate protection.	Protects parts from water, dust or chemical damage.
		Heat reflective.	Protects parts from heat.
		Non-flammable.	Will not aid combustion.
	Acrylic adhesive.	Long ageing.	Reduces cost of replacing damaged parts.
Specifications	Flame resistant U.L. Approved Class "L" low flammability.	No. 431 passed all requirements in accordance with F.A.A. Regulation No. 25, Paragraph 28.853. These tests, which include	flame retardant properties, are required on all materials used in cabin exteriors of commercial aircraft.

3M is a trademark of the 3M Company.

Values presented have been determined by standard test methods and are average values not to be used for specification purposes. Our recommendations on the use of our products are based on tests believed to be reliable but we would ask that you conduct your own tests to determine their suitability for your applications. This is because 3M cannot accept any responsibility or liability direct or consequential for loss or damage caused as a result of our recommendations.



Specialty Tapes & Adhesives

© 3M United Kingdom PLC 1996

3M United Kingdom PLC
3M House,
28 Great Jackson Street,
Manchester,
M15 4PA

Customer Service :

Tel 0161 236 8500
Fax 0161 237 1105

3M Ireland
3M House, Adelphi Centre,
Upper Georges Street,
Dun Laoghaire, Co. Dublin,
Ireland

Customer Service :

Tel (01) 280 3555
Fax (01) 280 3509