

InfraSolution X™

Integrated IT Access Control & Monitoring

AUSTIN
HUGHES

**Providing data
centre managers
and rack level
administrators
secure, IT Access
Control and
Environment
Monitoring
over Ethernet**



Unauthorised access and environmental conditions for Temperature and Humidity can be sent to the administrators via e-mail, SNMP, or SMS

HID®, MiFare™ Swipe Card Access with Easy to setup Designated Users with Access rights for individual racks at specific time / day / date



InfraSolution provides total reporting with complete access logs and event occurrences, the simple GUI software allows up to 8 simultaneous users access to control different cabinets

InfraPower PDU Monitoring & Control using centralised management, view, current (Amp), voltage (Volts), power (KW), energy consumption (kWh), and remotely switch on or off power sockets via overs IP

sensors



Swipe card locking with secure smart card technology using an Electromagnetic door handle



Temperature and Humidity Sensor



Water Sensor



Beacon



Smoke Detector



Shock Sensor



Infra Solution X Series

Control Box

AH-IS-X1000	InfraSolution Basic Version
AH-IS-X2000	InfraSolution Enhanced Version with multifunction module
AH-IS-800M	InfraSolution Mifare Handles Pair
AH-IS-800P	InfraSolution Proximity Handles Pair
AH-IS-XDSW	Infrasolution Mechanical Door Switch, 2m Cord, Pair
AH-IS-XDSI	Infrasolution Inductive Sensor, Pair
AH-IS-XDSS	Infrasolution Silicon Button Sensor, Pair

Sensors

AH-IG-TH01-2M	IG-TH01-2M Temperature and Humidity Sensor, 2m Cable
AH-IG-TH01-4M	IG-TH01-4M Temperature and Humidity Sensor, 4m Cable
AH-IG-T01-2M	IG-T01-2M Temperature Sensor, 2M Cable
AH-IG-T01-4M	IG-T01-4M Temperature Sensor, 4m Cable
AH-IG-S01-1M	IG-S01-1M Smoke Sensor, 1m Cable
AH-IG-S01-3M	IG-S01-3M Smoke Sensor, 3m Cable
AH-IG-V01-1M	IG-V01-1M Shock Sensor, 1m Cable
AH-IG-V01-3M	IG-V01-3M Shock Sensor 3m Cable
AH-IG-W01-3M	IG-W01-3M 5m Rope Type Water Sensor, IP68 connection and 3m Cat6 Cable
AH-IG-LP01-1M	IG-LP01-1M LED Lamp, 1m Cord, ON/OFF via Software or Door Sensor
AH-IG-LP01-3M	IG-LP01-3M LED Lamp, 3m Cord, ON/OFF via Software or Door Sensor
AH-IG-LP01/SW-1M	IG-LP01/SW-1M LED Lamp, 1m Cord, ON/OFF with switch
AH-IG-LP01/SW-3M	IG-LP01/SW-3M LED Lamp, 3m Cord, ON/OFF with switch
AH-IG-FB03-1M	IG-FB03-1M Flashing LED Beacon, 1m Cord
AH-IG-FB03-3M	IG-FB03-3M Flashing LED Beacon, 3m Cord

Software

AH-IS-X-ISM-20+5	InfraSolution X Series Manager, 5 Client users for 20 cabinets
AH-IS-X-ISM-50+5	InfraSolution X Series Manager, 5 Client users for 50 cabinets
AH-IS-X-ISM-100+5	InfraSolution X Series Manager, 5 Client users for 100 cabinets
AH-IS-X-ISM-300+5	InfraSolution X Series Manager, 5 Client users for 300 cabinets
AH-IS-X-ISM-500+10	InfraSolution X Series Manager, 10 Client users for 500 cabinets
AH-IS-X-ISM-1000+10	InfraSolution X Series Manager, 10 Client users for 1000 cabinets
AH-IS-X-C005	Additional Client Licenses, 5 additional users
AH-IS-X-N050	Additional Node Licenses, 50 Cabinets

