

## **ETP-400 (MOD2) – Single Button OEM Emergency Phone**

### **Description**

The **ETP-400 (MOD2)** is an outdoor-rated, hands-free OEM Emergency Phone. With components connected via extended wiring, it allows for custom mounting in virtually any application.

### **Features**

- Vandal resistant metal call button
  - Uses regular phone lines or PBX
  - Phone line powered: no power supply or battery back-up needed
  - Auxiliary input and outputs to integrate with CCTV, Blue Light Strobe, Scream Alert™ and other devices
  - Push button to call, then speak hands-free
  - LED indicator for hearing impaired
  - Built-in auto-dialer can dial two numbers: if first number doesn't answer or is busy, dials second number.
  - Auto-answer allows security to monitor and initiate calls with Emergency Phone
- Options available that offer the ability to automatically identify attendant of location of calling phone by recorded message and digital display



### **Specifications**

Dimensions:	Box - 6.56(167) W x 9.75(248) H x 2.5(64) D in(mm)
	Speaker - ø3.55(ø90), 3.45(88) W x 3.45(88) H in(mm)
	Microphone - 1.575(40) W x 0.90(23) H x 0.5(13) H in(mm)
	LED Board- 0.90(23) W x 0.39(10) H x 0.75(19) D in(mm)
	Button - ø0.75(ø19) in(mm), 5/8-24 hex nut
Weight:	4 lbs. (1.8 kg)
Operating Temperature:	-4°F to +149°F (-20°C to +65°C)
Communication:	2-way hands-free communication
Digit Capacity:	Up to 18 digits, including pauses, for each of two phone numbers
Dialing Speed:	Approximately 10 tones per second
Power Source:	Phone line powered (requires 20mA at 24 v off-hook)
Connection:	Parallel tip and ring connected to RJ11 connector for quick installation
Circuit Protection:	Varistor lightning suppressed and full wave polarity guarded
Programming:	Non-volatile EEPROM programming can be done from any telephone. No battery back-up is needed
"On Time":	Programmable from 1-4270 minutes in 1-minute increments.
Wiring Requirements:	1 twisted-shielded pair
Compliance:	CSA Certified to UL Standard 60950


### **Options & Accessories**

Voice Location Identifier:	Model <b>ETP-400V(MOD2)</b> includes the capability to record a message identifying the location of the call. Message is recorded and duration set during programming.
8-Line Consolidator:	Model <b>EC-8</b> allows connection of up to 8 phones on one phone line while retaining ability to call each phone individually. Can also create a closed system without need for any phone lines.
Monitoring/Diagnostic Software Package:	Talk-A-Lert®, model <b>ETP-TAL</b> , automatically polls each Emergency Phone, reports incoming calls and keeps permanent records of all events

Copyright 2009 Talk-A-Phone Co. All rights reserved.

# ETP-400 (MOD2) – Single Button OEM Emergency Phone

## Dimensions



Copyright 2009 Talk-A-Phone Co. All rights reserved.

Talk-A-Phone Co. • 7530 North Natchez Avenue • Niles, Illinois 60714-3804  
Phone 773.539.1100 • Fax 773.539.1241 • info@talkaphone.com • www.talkaphone.com  
All prices and specifications are subject to change without notice.  
Talk-A-Phone, Talk-A-Lert, Scream Alert and WEBS are registered trademarks of Talk-A-Phone Co.