

EN1249 Billtrap Transmitter

www.boschsecurity.com



BOSCH

Invented for life



The EN1249 Billtrap Transmitter provides the best range and reliability available today with the same profile and ruggedness as a hardwire billtrap. It can be used in any financial or retail environment.

System overview

Powered by Inovonics

The Inovonics EchoStream platform, powered by Inovonics wireless mesh network technology, ensures superior range, reliability, and scalability for commercial applications. Using a wide range of transmitters and repeaters, this proven technology provides flexibility and performance to meet the most stringent requirements. This exclusive protocol is available only on Inovonics EchoStream products.

Wireless 900 MHz Band

The Inovonics EchoStream platform sends redundant information on several multi-frequency channels within the FCC Part 15 900 MHz band, providing superior range and reliability. In comparison, systems that use a single frequency technology can only send information on one narrow band channel. Any interference within the band can cause missed signals. With wireless registration, it is easy to add this technology to any application.

- ▶ Reliable communication through 900 MHz spread spectrum technology with frequency hopping
- ▶ False alarm reduction through 56 bit communication protocol and advanced signal processing
- ▶ Fully supervised with transmitter check-in once per minute
- ▶ Armed confirmation through 2 and 10 sec smart baiting LED
- ▶ Slim profile

Functions

Supervision

The battery activity and radio link are supervised. Monitoring helps ensure reliable operation and safeguards against undetected loss of service due to end user damage such as dropping the billtrap repeatedly, exposing it to extreme temperature, getting the billtrap wet, or other similar events.

Certifications and approvals

Inovonics Wireless Corporation holds the following approvals:

FCC Conforms to FCC Part 15 regulations

Installation/configuration notes

Compatibility Information

The EN1249 Billtrap Transmitter is compatible with the following products:

Receivers

EN4016SK	Survey Receiver
EN4200	Serial Receiver
EN4204R	LED Receiver

Repeater

EN5040-T	High-power Repeater
----------	---------------------

Parts included

Quantity	Component
1	Billtrap
1	Battery

Technical specifications**Electrical**

Power:	3.0 VDC, 60 mA
Battery Replacement:	Duracell DL123A, PanasonicCR123A, or approved equivalent. Not all brands are equivalent. Use the brands specified.
Battery Life (Average):	3 to 4 years. Typical battery life shown is for supervised operation.

Mechanical

Dimensions:	15.7 cm x 8.9 cm x 2.3 cm (6.2 in. x 3.5 in. x 0.9 in.)
-------------	--

Environmental

Relative Humidity:	Up to 90%, non-condensing
Temperature (Operating):	0°C to +60°C (-4°F to +140°F)

Transmission Characteristics

Frequency:	902 MHz to 928 MHz
------------	--------------------

Trademarks

Trademark names are used throughout this document. In most cases, these designations are claimed as trademarks or registered trademarks in one or more countries by their respective owners. Rather than placing a trademark symbol in every occurrence of a trademark name, Bosch Security Systems, Inc. uses the names only in an editorial fashion and to the benefit of the trademark owner with no intention of infringing the trademark.

Duracell is a registered trademark of the Gillette Company, USA, in the United States and/or other countries.

Inovonics is a trademark of Inovonics Wireless Corporation.

Panasonic is a registered trademark of Matsushita Electric Industrial Co., Ltd.

Ordering information**EN1249 Billtrap Transmitter**

Provides the range and reliability of hardwire billtraps.
Order number **EN1249**

Represented by:

Americas:

Bosch Security Systems, Inc.
130 Perinton Parkway
Fairport, New York, 14450, USA
Phone: +1 800 289 0096
Fax: +1 585 223 9180
security.sales@us.bosch.com
www.boschsecurity.us

Europe, Middle East, Africa:

Bosch Security Systems B.V.
P.O. Box 80002
5617 BA Eindhoven, The Netherlands
Phone: + 31 40 2577 284
Fax: +31 40 2577 330
emea.securitysystems@bosch.com
www.boschsecurity.com

Asia-Pacific:

Robert Bosch (SEA) Pte Ltd, Security
Systems
11 Bishan Street 21
Singapore 573943
Phone: +65 6571 2808
Fax: +65 6571 2699
apr.securitysystems@bosch.com
www.boschsecurity.asia

China:

Bosch (Shanghai) Security Systems Ltd.
201 Building, No. 333 Fuquan Road
North IBP
Changning District, Shanghai
200335 China
Phone +86 21 22181111
Fax: +86 21 22182398
www.boschsecurity.com.cn

America Latina:

Robert Bosch Ltda Security Systems Division
Via Anhanguera, Km 98
CEP 13065-900
Campinas, Sao Paulo, Brazil
Phone: +55 19 2103 2860
Fax: +55 19 2103 2862
latam.boschsecurity@bosch.com
www.boschsecurity.com