

Weatherproof Alarm Sirens

Thank you for your choice of Speco Technologies' **SA4P/SA5P** Sirens. These units are designed and manufactured to provide a compact source for any alarm application. The weatherproof ABS construction ensures long-life in outdoor environments, but the **SA4P/SA5P** are also suitable for indoor or mobile use.

INSTALLATION INSTRUCTIONS:

- 1) The **SA4P/SA5P** are constructed with a pivoting, metal base.
- 2) Loosen the nut connecting the metal base to the horn to pivot the base to the desired angle.
- 3) Tighten the nut to lock the horn at the desired angle.
- 4) The base contains 3 holes for screws. Use screws with at least ¼" diameter head to ensure safe installation.
- 5) Connect the red (positive) and black (negative/ground) wires to the corresponding connections on your 6-12V DC power supply or source.

SPECIFICATIONS:

SA4P

- Current Rating: 750mA
- dB Rating: 120
- Warbling Tone
- Operating Voltage: 6V to 12V DC
- Max Power: 20 W
- Size: 4" Diameter x 4" Length
- Weatherproof ABS construction



SA₅P

- Current Rating: 750mA
- dB Rating: 115
- Warbling Tone
- Operating Voltage: 6V to 12V DC
- Max Power: 20 W
- Size: 5" Diameter x 5-7/8" Length
- Weatherproof ABS construction



WARRANTY INFORMATION:

We warranty this product to be free from any manufacturing or material defects for two (2) years from the date of purchase.

This warranty will not extend to any products which have been subjected to misuse, neglect, accident, or improper installation, used in violation of instructions furnished by us; or to units which have been repaired or altered outside of the factory. This limited warranty does not apply to broken cases, batteries, or other physically damaged parts. If a Speco Technologies product is purchased from an unauthorized distributor or other source, including RETAILERS, MAIL ORDER SELLERS and ONLINE SELLERS, it will not be honored or serviced under existing Speco Technologies warranty policy. Any sale of products by an unauthorized source or other manner not authorized by Speco Technologies will void the warranty on the applicable product.

Upon request by customer, Speco Technologies ("The Company") will, at customer's expense, repackage merchandise in new cartons, replace missing accessories, and return in resalable condition. Unless requested, the company will replace and return all merchandise in the packaging in which it was received. This warranty is in lieu of all expressed warranties, expressed or implied, and of all obligations or liability on our part, and we neither assume nor authorize any representative or other person to assume for us any obligation or liability. In no event shall we be liable for incidental or consequential damages arising from the use of the product, or for any delay in the use of this product due to causes beyond our control. Some states do not allow limitations of how long an implied warranty lasts and/or do not allow the exclusion or limitation of consequential damages. The above limitations on implied warranty and consequential damages may not apply to you. This warranty gives you specific legal rights. You may have other rights which vary from state to state. This limited warranty extends to products listed in the company's current price schedule.

 $\label{thm:constantly} Speco\ Technologies\ is\ constantly\ developing\ and\ improving\ products.$

We reserve the right to modify product design and specifications without notice and without incurring any obligation.

Speco Technologies . 200 New Highway . Amityville . NY . 11701 . www.specotech.com