

Part Number	G2215 -- EGVHVBAN152-104UKLUK-V Basic, Non-Surge
Power Configuration	13A, 230V, 2.9kW
Physical Configuration	66 in / 1682 mm Vertical



Description	The G2215 -- EGVHVBAN152-104UKLUK-V non-surge unit is ideal for facilities already equipped with surge protection.
Product Summary	G2215 -- EGVHVBAN152-104UKLUK-V - Non-Surge, 13A, 230V, Vertical, (15) BS1363, 3 m power cord with BS1363, Current - Local Digital RMS Current Meter +/- 2% Accuracy with Full Scale 60Hz sine wave input , Aggregate - Total Unit Monitoring
Monitoring	Current - Local Digital RMS Current Meter +/- 2% Accuracy with Full Scale 60Hz sine wave input
Plug Form	 BS1363
Receptacle	 BS1363 (Quantity: 15)



G2215 -- EGVHVBAN152-104UKLUK-V - Product Specification and Options

Monitoring	Current - Local
	Digital RMS Current Meter +/- 2% Accuracy with Full Scale 60Hz sine wave input
Monitoring Level 1	Aggregate - Total Unit Monitoring
Quantity Of Inputs	1
Voltage	230V
Current	13A
VA per Input (Load Capacity)	2.9kW
Frequency	50/60 Hz
Over Current Protection	None
Switch	No
Power Cable Wire Gauge	1.5mm ² PVC
Power Cable Length	3m
Plug Type	BS 1363P
Receptacle/Socket Type #1	BS1363
Quantity on Face #1	15
Style #1	Individual - Left Hand Angled
Maximum Output per Receptacle/Socket #1	13A
Voltage per Receptacle/Socket #1	230V
Heavy Steel -Black Powder Coat	Yes
Configuration	66in / 1682mm Vertical Rackmount
GE Vertical Mounting Bracket	Yes
Toolless Mounting Hardware - Center to Center Spacing	1556 mm and 1645 mm
Product Warranty	Three Year
Certification/Agency Approvals	CE Marked
Certification/Agency Approvals	Complies with EN 55022 and EN 55024
Certification/Agency Approvals	RoHS Compliant
Chassis Dimensions (LxWxD)	1682mm x 54mm x 50mm
Shipped Weight	13lbs (5.9kg)

Geist Americas

1821 Yolande Ave
Lincoln, NE 68521 USA
1.800.432.3219 or
1.402.474.3400
www.geistglobal.com

Geist Europe

Unit 1, The Monarch Centre,
Venture Way,
Priorswood, Taunton,
Somerset, TA2 8DE UK
+44 (0) 1823 275100
www.geisteurope.com

Geist Asia

China
Tiley Plaza Bldg. A, Unit #2808,
No. 199 Haide 3 Road,
Nanshan Shenzhen,
Guangdong Province, China.
Postal Code: 518000
Tel: +86.755.86639505
www.geistglobal.com

Geist Asia

Hong Kong
Tel: +852 90361927
Email: salesasia@geistglobal.com