



Part Number G2218 -- EGVHVBAN202-102UKRPS6-IP44  
 Basic, Non-Surge  
 Power Configuration 16A, 230V, 3.6kW  
 Physical Configuration 66 in / 1682 mm Vertical



Description	The G2218 -- EGVHVBAN202-102UKRPS6-IP44 non-surge unit is ideal for facilities already equipped with surge protection.
Product Summary	G2218 -- EGVHVBAN202-102UKRPS6-IP44 - Non-Surge, 16A, 230V, Vertical, (20) BS1363, 3 m power cord with 2P+E, Current - Local  Digital RMS Current Meter +/- 2% Accuracy with Full Scale 60Hz sine wave input, , Aggregate - Total Unit Monitoring
Monitoring	Current - Local  Digital RMS Current Meter +/- 2% Accuracy with Full Scale 60Hz sine wave input
Plug Form	 2P+E
Receptacle	 BS1363 (Quantity: 20)

## G2218 -- EGVHVBAN202-102UKRPS6-IP44 - Product Specification and Options

Monitoring	Current - Local Digital RMS Current Meter +/- 2% Accuracy with Full Scale 60Hz sine wave input
Monitoring Level 1	Aggregate - Total Unit Monitoring
Quantity Of Inputs	1
Voltage	230V
Current	16A
VA per Input (Load Capacity)	3.6kW
Frequency	50/60 Hz
Over Current Protection	None
Switch	No
Power Cable Wire Gauge	2.5mm <sup>2</sup> H07RN-F
Power Cable Length	3m
Plug Type	IEC60309 2P + E, 16A, 250V, Splashproof IP44
Receptacle/Socket Type #1	BS1363
Quantity on Face #1	20
Style #1	Individual - Right Hand Angled
Maximum Output per Receptacle/Socket #1	13A
Voltage per Receptacle/Socket #1	230V
Heavy Steel -Black Powder Coat	Yes
Configuration	66in / 1682mm Vertical Rackmount
GE Vertical Mounting Bracket	Yes
Toolless Mounting Hardware - Center to Center Spacing	1556 mm and 1645 mm
Product Warranty	Three Year
Certification/Agency Approvals	CE Marked
Certification/Agency Approvals	Complies with EN 55022 and EN 55024
Certification/Agency Approvals	RoHS Compliant
Chassis Dimensions (LxWxD)	1682mm x 54mm x 50mm
Shipped Weight	14lbs (6.35kg)

### Geist Americas

1821 Yolande Ave  
Lincoln, NE 68521 USA  
1.800.432.3219 or  
1.402.474.3400  
www.geistglobal.com

### Geist Europe

Unit 1, The Monarch Centre,  
Venture Way,  
Priorswood, Taunton,  
Somerset, TA2 8DE UK  
+44 (0) 1823 275100  
www.geisteurope.com

### Geist Asia

China  
Tiley Plaza Bldg. A, Unit #2808,  
No. 199 Haide 3 Road,  
Nanshan Shenzhen,  
Guangdong Province, China.  
Postal Code: 518000  
Tel: +86.755.86639505  
www.geistglobal.com

### Geist Asia

Hong Kong  
Tel: +852 90361927

Email: salesasia@geistglobal.com