



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT P/N	WEIGHT
UIT70FV2	.07 LB/PC (35g/PC)
OF70FV2	

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. THE UIT70FV2 ACCEPTS TWO (2) MINI-COM MODULES.
3. DIMENSIONS IN PARENTHESIS ARE IN METRIC.
4. THE UIT70FV2 FACEPLATE CAN BE USED WITH PANDUIT SURFACE RACEWAY SYSTEMS AND BOXES THAT ACCEPT 70mm SNAP-ON FACEPLATES (INCLUDES: T-70, TWIN-70, TE70, TG-70, ETC.)
5. POCKET TO BE USED WITH PANDUIT PART NUMBER UILC1**.
6. POCKET TO BE USED WITH PANDUIT PART NUMBER UILC2**.
7. POCKETS TO BE USED WITH PANDUIT PART NUMBER UICIB**, UICIP**, OR UICID**.
8. THE OF70FV2 FACEPLATE CAN BE USED WITH PANDUIT OFFICE FURNITURE CORNER RACEWAY.



CAD FILENAME/LAYERS		D38316BD_DC_UIT70FV2_01B.prt	
PANDUIT		CORP TINLEY PARK, ILLINOIS	
ULTIMATE I.D. TWO MINI-COM MODULE VERTICAL SLOPED SNAP-ON FACEPLATE (UIT70FV2 & OF70FV2)		CUSTOMER DRAWING	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± (.XX) ± .03(.8) ANGLES ±		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
2	04-25-03	JBN	PM
1	07-10-02	JHEP	RGRO
R	12-06-01	MSO	CEO
REV	DATE	BY	CHK
D. ADDED NOTE 8 C. ADDED PART NUMBER OF70FV2		38316-07 RGRO RGRO	
B. REVISED NOTE 5 A. REVISED MODEL		38316-07 RGRO	
RELEASED TO PRODUCTION		38316-07 RGRO	
DESCRIPTION		ECN - R CUST SUP GMBH	
DRAWN BY		MAT'L:	
MSO		PVC	
DATE		SCALE	
12-06-01		NONE	
CHK'D		DRAWING NO.	
CEO		38316-07	
		DWG	
		A	
		SIZE	