



Hand-Held
Thermal Transfer
Printing Solutions



PanTher™ LS8E **Cougar™ LS9**

	PanTher™ LS8E	Cougar™ LS9
Network Component Labels	Pages O.3 – O.4	
Self-Laminating Labels	Page O.5	
Die-Cut Nylon Cloth	Page O.7	
Continuous Nylon Cloth Tape	Page O.7	
Die-Cut Heat Shrink Label Cassettes	Page O.8	Page O.8
Continuous Heat Shrink Label Cassettes	Page O.9	Page O.9
Continuous Tape Cassettes	Page O.10	Page O.10
Ultimate ID® Label Cassettes	Page O.11	Page O.11
Turn-Tell® Labels	Page O.17	
Marker Plates	Page O.18	
Flag Labels	Page O.18	

P1™ Network Component Label Cassettes for PanTher™ LS8E Hand-Held Thermal Transfer Printer



- P1™ Label Cassette contains an integrated memory device for automatic formatting, recall of last legend used, and number of labels remaining in the cassette
- Fast loading label cassette includes both label material and ribbon to make changing labels easy
- Use for identifying patch panels, faceplates, punchdown blocks and other network systems hardware
- Die-cut labels designed to provide maximum aesthetic quality and appearance
- Available in adhesive polyolefin and non-adhesive polyester materials

<i>Application Description</i>	<i>Typical Application Page</i>	<i>Code</i>
Boxes – Surface Mount, Outlet, Hybrid	G.24	BX
Faceplates	G.2	FP
GP6™ Category 6 Punchdown Blocks	B.72	GP
Jack Modules	B.12	JM

<i>Application Description</i>	<i>Typical Application Page</i>	<i>Code</i>
Punchdown Blocks – 110	B.80	PB
Patch Panels	B.26 – B.27	PP
Racks and Cabinets	L.11	RK
Cable Marker Holder – SLCT	B.90	SL

Part Number	Part Description	Width		Height		Std. Pkg. Qty.	Std. Ctn. Qty.
		In.	mm	In.	mm		
C061X030FJC	White, adhesive polyolefin label, 500/cassette, Mini-Com® 1-port identifier. Application codes: BX, FP, and PP.	0.61	15.5	0.30	7.6	1	10
C125X030FJC	White, adhesive polyolefin label, 200/cassette, Mini-Com® 2-port identifier. Application codes: BX, FP, and PP.	1.25	31.8	0.30	7.6	1	10
C138X019FJC	White, adhesive polyolefin label, 200/cassette, Mini-Com® Module identifier. Application code: JM.	1.38	35.1	0.19	4.8	1	10
C150X030Y1C	White, non-adhesive polyester label, 75/cassette, Mini-Com® 3-port identifier. Application codes: FP.	1.50	38.1	0.30	7.6	1	10
C188X030FJC	White, adhesive polyolefin label, 150/cassette, Mini-Com® 3-port identifier. Application code: FP.	1.88	47.8	0.30	7.6	1	10
C195X040Y1C	White, non-adhesive polyester label, 100/cassette, single-gang faceplate. Application code: FP.	1.95	49.5	0.40	10.2	1	10
C200X100FJC	White, adhesive polyolefin label, 150/cassette, SLCT bundle marker identifier. Application code: SL, RK.	2.00	50.8	1.00	25.4	1	10
C252X030FJC	White, adhesive polyolefin label, 125/cassette, Mini-Com® 4-port identifier. Application codes: BX, FP, and PP.	2.52	64.0	0.30	7.6	1	10

Order number of cassettes required.

Table continues on next page

