

## ST2MT Installation Tool

- Cable tie side entry for immediate positioning of tie and tool
- One hand operation – lightweight
- Easy removal of excess tie



- Tool tension is controlled by installer – twist action cut-off
- Rugged, lightweight, easy-to-operate pliers-type tool provides mechanical advantage

| Part Number | Part Description                                                                                                                                                | Std. Pkg. Qty. |
|-------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------|
| ST2MT       | Used with standard, light-heavy, heavy and extra-heavy cross section Pan-Steel® type MLT ties, type MLTC/MLTFC coated ties, and type MLTDH double wrapped ties. | 1              |

## RT2HT and RT2HTN Installation Tools

- Cable tie side entry for immediate positioning of tie and tool to speed installation
- Multi-position rear handle provides flexibility for a one or two hand installation



RT2HT



RT2HTN

- Narrow nose tool design option available for applications requiring installations in tight confined spaces
- Replacement cutter blade and handle available for RT2HT

| Part Number | Part Description                                                                                                                                                             | Std. Pkg. Qty. |
|-------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------|
| RT2HT       | Used with extra-heavy, extra-heavy 15, and super-heavy cross section Pan-Steel® type MLT and MLTFC ties. Width of tool nose 2.60" (66.0mm).                                  | 1              |
| RT2HTN      | Narrow nose installation tool for use with extra-heavy, extra-heavy 15, and super-heavy cross section Pan-Steel® type MLT and MLTFC ties. Width of tool nose 1.06" (27.0mm). | 1              |

## HTMT Installation Tool

- Economical
- Coiled tie end remaining after tensioning assures a safe end



- Manual tension, no cut-off
- Installs ties parallel to the bundle

| Part Number | Part Description                                                                                                                                    | Std. Pkg. Qty. |
|-------------|-----------------------------------------------------------------------------------------------------------------------------------------------------|----------------|
| HTMT        | Used with standard, light-heavy, and heavy cross section Pan-Steel® type MLT ties, type MLTC/MLTFC coated ties, and type MLTDH double wrapped ties. | 1              |

A.  
System  
Overview

B1.  
Cable  
Ties

B2.  
Cable  
Accessories

B3.  
Stainless  
Steel Ties

C1.  
Wiring  
Duct

C2.  
Surface  
Raceway

C3.  
Abrasion  
Protection

C4.  
Cable  
Management

D1.  
Terminals

D2.  
Power  
Connectors

D3.  
Grounding  
Connectors

E1.  
Labeling  
Systems

E2.  
Labels

E3.  
Pre-Printed  
& Write-On  
Markers

E4.  
Permanent  
Identification

E5.  
Lockout/  
Tagout  
& Safety  
Solutions

F.  
Index