


1000 TVL Indoor/Outdoor IR Vandal Resistant Bullet with True WDR

HT7040K 2.8-12mm auto-iris varifocal lens, dark grey housing



Features

- 1/3" 1.3MP Sony Sensor
- 1000 TV lines highest resolution in analog
- True WDR functionality
- 12VDC & 24VAC dual voltage operation
- Vandal / tamper resistant operation
- IP67 compliant
- 5 year warranty

Specifications

Image Sensor	1/3" 1.3MP Sony Sensor	Brightness.....	0 - 20 (level adjustable)
Resolution.....	1000 TV lines	AGC.....	0 - 20 (level adjustable)
Minimum Illumination.....	0 lux (IR LEDs on)	Smart-IR.....	0 - 20 (level adjustable)
Effective Pixels	1305 (H) x 1049 (V)	Sense-Up.....	(x2 – x32)
Total Pixels	1312 (H) x 1069 (V)	Motion Tracking	On / Off
TV System	NTSC	Motion Detection.....	On / Off (4 zones)
Scanning System.....	Progressive	Privacy.....	On / Off (16 zones)
Number IR LEDs	42	Mirror / V-Flip.....	On / Off
IR Range	Up to 98 ft. (depending on scene reflection)	Sharpness	0 - 15 (level adjustable)
IR LED Wavelength	850m	Lens Shading Compensation	On / Off
S/N Ratio	More than 50dB	3DNR.....	Off / Low / Middle / High
Frame Rate.....	Max 50P/60P	Defog.....	On (Auto / Manual) / Off
Video Output.....	1.0Vp-p / 75 ohms	DIS.....	On / Off
Lens.....	DC / Manual	Power Supply	12VDC / 24VAC dual voltage operation (power supply not included)
Electronic Shutter Speed.....	Auto / Manual (1/60 sec. - 1/60,000 sec.) / Flicker	Power Consumption	12VDC, 450mA / 24VAC, 190mA
WDR.....	On (Low / Middle / High) / Off	Operating Temperature.....	-4° F – 140° F
Digital WDR.....	On (Low / Middle / High) / Off	Dimensions.....	3.94" (W) x 3.94" (H) x 8.27" (L)
Day/Night.....	Color / BW / Auto / Ext	Weight	3.09" lbs.
White Balance	Auto / Auto Ext / AWC – SET / Manual		

Optional Accessories



INTJBS
Square
Junction Box



INTCM
Corner/Pole
Adaptor



CVCJBB
Bullet Camera
Junction Box



PSW4
24VAC
Power Supply



PSW5
12VDC
Power Supply



Speco Technologies is constantly developing and improving products. We reserve the right to modify product design and specifications without notice and without incurring any obligation. Spec Rev. 2/11/14