

AC-90 Multipurpose Lubricant ® Industrial Spray



AC-90 is the No. 1 choice multipurpose lubricant. AC-90 is an industrial spray lubricant. AC-90 does not contain Silicone or CFC's. AC-90 will penetrate and release rusty and/or jammed components. AC-90 displaces moisture from vehicle ignitions systems and aids starting and smooth running. Simply spray AC-90 over the exterior of all distributor leads, spark plug leads and all electrical components to prevent moisture induced faults.

AC-90 cleanly lubricates and restores smooth, silent operation to hinges, locks castors, drawer runners, and curtain tracks. AC-90 multipurpose lubricant will stop sticking and squeaking. AC-90 cleans all metals and removes bloom from enamel surfaces such as fridges, cookers, and stainless steel sinks. AC-90 removes dirt, grime, lime scale, crayon marks, chewing gum, and adhesives. AC-90 degreases and leaves an anti-rust protective film. AC-90 is ideal for protecting metal components during storage or manufacture. De-scales taps and showers. Does not conduct electricity within the normal range found in home or industry. AC-90 is the perfect multipurpose lubricant cleaner formulation for all around the workshop, garage, and factory. Unlike other multipurpose industrial spray lubricants.

AC-90 does not contain Odourless Kerosene which can give rise to skin problems. AC-90 is available in various size aerosols, with both standard propellant and with a special non flammable propellant which is Ideal for use in some industrial locations where a flammable propellant aerosol is considered inappropriate. AC-90 is also available in 5/25/200 litre drums available with a purpose made applicator which has all appropriate health and safety data printed on the body of the applicator. AC-90 Multipurpose lubricant is approved for quality by Jaguar Cars Limited, J.C.B., Audi Volkswagen, and British Gas. AC-90 formulation is the only lubricant /cleaner product approved by A.E. Technologies for use on the UK National Grid electrical system.

For users in the Food Industry AC-90 is also available in a H1 approved formulation which tasteless and odourless. See our food grade approved product range for more details.



425ml Aerosol Product Code 2006
500ml Aerosol Product Code 1839
250ml Aerosol CO² Non Flammable Propellant
Product Code 1850
500ml Aerosol CO² Non Flammable Propellant
Product Code 1779
5 litre Can Product Code 1224
25 litre Drum Product Code 1225
200 litre Drum Product Code 1226
Re-fillable Metal hand spray applicator with
permanently printed health and safety information on



Key Features:

- Does not contain Silicone or CFC
- Multi-purpose industrial spray lubricant/cleaner
- Strong water and moisture displacing action
- Penetrates rust and corrosion
- Cleans and Protects all metals against rust
- Suitable for electronic ignition systems



Application(s):

- Food Grade Products
- Anti-seize, Assembly, Dismantle
- Cleaners/Degreasers
- Corrosion Protection
- Electrical Products
- General Lubricant
- Release Fluids
- Welding Products
- Plumbing Products

Action Can Ltd.

Dixon Close, Old Boston Trading Estate, Haydock, St. Helens, England, WA11 9SF
Tel: 00 44 (0)1942 713667 Fax: 00 44 (0)1942 716235
Email: salesoffice@actioncan.com www.actioncan.com

