


Extend your reach with Greenlee Fish Poles



Now in Three Convenient Sizes...12', 18' and 24'

Whether you are trying to pull wires through a suspended ceiling or push wires under a sub-floor, Greenlee has the product for you! Greenlee now offers three Fish Poles, the new FP12 (12' Fish Pole), the FP18 (18' Fish Pole) and FP24 (24' Fish Pole). All three Fish Poles are designed specifically for pushing and pulling wires over long distances. To make maneuvering easier in cramped spaces, Greenlee made all of the models lightweight. The FP12 weighs less than 1-1/2 pounds, the FP18 weighs slightly over two pounds and the FP24 is less than five pounds!

Don't let the light weight fool you, these fish poles are made to handle the most rugged environment. In fact, the FP18 and the FP24 have an enhanced gripping section and all three models are made of durable fiberglass material designed for long-term use.

In addition to pulling and pushing wires, the special hook on these fish poles is convenient for installing and twisting hanger wires in suspended ceilings.

PRODUCT FEATURES

- **Push or pull wires over long distances** including suspended ceilings, sub-floors, crawl spaces and attics.
- **Non-conductive, high-impact** construction for long life.
- **Specialized hook** can be used to install wires in suspended ceilings.
- **Velcro strap secures pole** when in collapsed position.
- **Self-contained**, no loose parts.
- **Lightweight design** to minimize fatigue.
- **FP12** - 12' Fish Pole collapses to 26" x 1.25" and uses friction-locking system.
- **FP18** - 18' Fish Pole collapses to 27" x 2" and uses friction-locking system.
- **FP24** - 24' Fish Pole collapses to 50" x 2.25" and uses snap lock buttons to maintain extended reach capabilities.

ACCESSORIES

- Replacement hook - CAT/UPC NO.10453

SPECIFICATIONS

	FP12	FP18	FP24
Extended length:	12 ft. (3.7 m)	18 ft. (5.5 m)	24 ft. (7.3 m)
Collapsed length:	26 in. (660 mm)	27 in. (686 mm)	50 in. (1270 mm)
Diameter:	1.25 in. (32 mm)	2 in. (51 mm)	2.25 in. (57.1 mm)
Weight:	1.3 lb. (0.6 kg)	2.5 lb. (1.1 kg)	4.25 lb. (1.9 kg)

ORDERING INFORMATION

CAT NO.	UPC NO.	DESCRIPTION	QTY
FP12	02268	Fish Pole 12 ft.	1
FP18	10442	Fish Pole 18 ft.	1
FP24	10443	Fish Pole 24 ft.	1

DISTRIBUTED BY:



GREENLEE®
A Textron Company

USA 800-435-0786 Fax: 800-451-2632
815-397-7070 Fax: 815-397-1865
Canada 800-435-0786 Fax: 800-524-2853
International +1-815-397-7070 Fax: +1-815-397-9247

4455 Boeing Drive • Rockford, IL 61109-2988 • USA • 815-397-7070
©2005 Greenlee Textron Inc. • An ISO 9001 Company • Printed in USA
Greenlee Textron Inc. is a subsidiary of Textron Inc.

www.greenlee.com

MA-4471 08/05