

B430 Plug-in Telephone Communicator

www.boschsecurity.com



BOSCH

Invented for life



- Provides a single telephone line with RJ-45 connection for central station reporting and remote programming
- Easily configured for communications from Remote Programming Software (RPS) or a keypad, eliminating the need for separate configuration
- Easy two-step plug-in installation, troubleshooting, and maintenance

The B430 provides communication over the PSTN (Public Switched Telephone Network) by connecting the PSTN to the control panel. The module provides a single telephone jack, and easily installs into the control panel's on-board plug-in module connector.

Functions

Central station reporting

The B430 supports reporting to a central station receiver through the telephone lines.

Remote programming of Bosch control panels

The B430 supports secure RPS programming of compatible Bosch control panels.

Certifications and approvals

Region	Agency	
US	UL	UL 365 - Police Station Connected Burglar Alarm Units and Systems
		UL 636 Holdup Alarm Units and Systems
		UL 985 - Household Fire Warning System Units
		UL 1023 - Household Burglar-Alarm System Units

	FCC	UL 1076 - Proprietary Burglar Alarm Units and Systems
		UL 1610 - Central-Station Burglar-Alarm Units
Canada	ULC	FCC, Part 15 FCC, Part 68 FCC Registration Number: ESVAL00BB430 Ringer Eq: 0.0B
		ULC C1023 - Household Burglar Alarm System Units
		ULC C1076 - Proprietary Burglar Alarm Units and System
		ULC S303 - Local Burglar Alarm Units and System
	IC	ULC S304 - Central and Monitoring Station Burglar Alarm Units
		ULC S545 - Residential Fire Warning System Control Units
		ICES-003

Region	Certification	
USA	CSFM	7167-1615:0247 7167 -- CONTROL UNIT (HOUSEHOLD)
	FDNY-CoA	#6174 UL 864 9th Edition
Brazil	ANATEL	1709-13-1855

Installation/configuration notes

Mounting considerations

You can mount the B430 Plug-in Telephone Communicator in any B Series control panel, which can then be mounted in a variety of enclosures for optimal situations.

Wiring considerations

The B430 connects to the B Series control panel without tools or physical wiring for power. It has an RJ-45 jack for plugging in the phone line (PSTN).

Compatibilities

Control panels	B5512 Control Panels
	B4512 Control Panels
	B3512 Control Panels
Phone cords	D161 Modular Telephone Cord
	D162 Modular Telephone Cord
Phone jack	D166 Telephone Jack

Parts included

Quantity	Component
1	B430 Plug-in Telephone Communicator
1	Literature pack

Technical specifications

Electrical

Current (maximum)	24 mA
Voltage (operating)	12 V nominal
Communication speed	2400 baud maximum

Environmental

Relative humidity	5 – 93% at +90°F (+32°C) non-condensing
Operating temperature	+32°F to +120°F (0°C to +49°C)

Mechanical

Board Dimensions	2 in x 3.68 in x 0.60 in (50 mm x 93.5 mm x 15.25 mm)
------------------	---

Represented by:

Americas:

Bosch Security Systems, Inc.
130 Perinton Parkway
Fairport, New York, 14450, USA
Phone: +1 800 289 0096
Fax: +1 585 223 9180
security.sales@us.bosch.com
www.boschsecurity.us

Europe, Middle East, Africa:

Bosch Security Systems B.V.
P.O. Box 80002
5617 BA Eindhoven, The Netherlands
Phone: + 31 40 2577 284
Fax: +31 40 2577 330
emea.securitysystems@bosch.com
www.boschsecurity.com

Asia-Pacific:

Robert Bosch (SEA) Pte Ltd, Security
Systems
11 Bishan Street 21
Singapore 573943
Phone: +65 6571 2808
Fax: +65 6571 2699
apr.securitysystems@bosch.com
www.boschsecurity.asia

China:

Bosch (Shanghai) Security Systems Ltd.
201 Building, No. 333 Fuquan Road
North IBP
Changning District, Shanghai
200335 China
Phone +86 21 22181111
Fax: +86 21 22182398
www.boschsecurity.com.cn

America Latina:

Robert Bosch Ltda Security Systems Division
Via Anhanguera, Km 98
CEP 13065-900
Campinas, Sao Paulo, Brazil
Phone: +55 19 2103 2860
Fax: +55 19 2103 2862
latam.boschsecurity@bosch.com
www.boschsecurity.com