

# BASIC PDU

**Density** Single-power inlet; 4-18 outlets per rack-mount 1.5U enclosure Max 36 outlet for vertical 0U models

**Power** 115VAC-230VAC, 50/60 Hz, 16 or 32-Amp power inlet options. Single or 3 phase option

## IEC C13 TYPE

Product Code	Product Description
PB-C06-010-116	1,5U 19" Aluminum 6 way with circuit breaker
PB-C06-100-116	1,5U 19" Aluminum 6 way with on/off switch (*)
PB-C08-010-116	1,5U Vertical Aluminum 8 way with circuit breaker
PB-C08-100-116	1,5U 19" Aluminum 8 way with on/off switch (*)
PB-C12-010-116	1,5U Vertical Aluminum 12 way with circuit breaker
PB-C16-010-132	1,5U Vertical Aluminum 16 way with circuit breaker
PB-C18-010-132	1,5U Vertical Aluminum 18 way with circuit breaker

## GERMAN TYPE (SCHUKO)

Product Code	Product Description
PB-S04-100-116	1,5U 19" Aluminum 4 way with on/off switch (*)
PB-S04-010-116	1,5U 19" Aluminum 4 way with circuit breaker
PB-S06-100-116-W	1U 19" Aluminum 6 way with on/off switch (*)
PB-S06-010-116-W	1U 19" Aluminum 6 way with circuit breaker
PB-S08-000-116-W	1U 19" Aluminum 8 way (*)
PB-S08-010-116-W	1U Vertical Aluminum 8 way with circuit breaker
PB-S08-100-116-W	1U 19" Aluminum 8 way with on/off switch (*)
PB-S12-010-116	1,5U Vertical Aluminum 12 way with circuit breaker
PB-S16-000-132	1,5U Vertical Aluminum 16 way (*)
PB-S16-010-132	1,5U Vertical Aluminum 16 way with circuit breaker
PB-S18-010-132	1,5U Vertical Aluminum 18 way with circuit breaker

## UK TYPE

Product Code	Product Description
PB-U05-100-113	1,5U 19" Aluminum 5 way with on/off switch (*)
PB-U05-010-113	1,5U 19" Aluminum 5 way with circuit breaker
PB-U07-100-113	1,5U Vertical Aluminum 7 way with on/off switch (*)
PB-U08-100-113	1,5U Vertical Aluminum 8 way with on/off switch (*)
PB-U08-010-113	1,5U Vertical Aluminum 8 way with circuit breaker
PB-U12-100-113	1,5U Vertical Aluminum 12 way with on/off switch (*)
PB-U12-010-113	1,5U Vertical Aluminum 12 way with circuit breaker
PB-U16-010-132	1,5U Vertical Aluminum 16 way with circuit breaker
PB-U18-010-132	1,5U Vertical Aluminum 18 way with circuit breaker

## FRENCH TYPE

Product Code	Product Description
PB-F06-100-116-W	1U 19" Aluminum 6 way with on/off switch (*)
PB-F06-010-116-W	1U 19" Aluminum 6 way with circuit breaker
PB-F08-100-116-W	1U 19" Aluminum 8 way with on/off switch (*)
PB-F08-010-116	1,5U Vertical Aluminum 8 way with circuit breaker
PB-F09-000-116-W	1U 19" Aluminum 9 way (*)
PB-F12-010-116	1,5U Vertical Aluminum 12 way with circuit breaker
PB-F16-010-132	1,5U Vertical Aluminum 16 way with circuit breaker

## UNIVERSAL TYPE

Product Code	Product Description
PB-E06-100-116	1U 19" Aluminum 6 way with on/off switch (*)
PB-E06-010-116	1U 19" Aluminum 6 way with circuit breaker
PB-E08-100-116	1U 19" Aluminum 8 way with circuit breaker
PB-E08-010-116	1U Vertical Aluminum 8 way with on/off switch (*)

**Minimum Order Quantity:**30 Pcs.

For other options please contact to your sales representative

Canovate can make changes without notification

\*Protection should be located in power distribution panel for the models without circuit breakers



[www.facebook.com/canovategroup](http://www.facebook.com/canovategroup)



[www.linkedin.com/company/canovate-group](http://www.linkedin.com/company/canovate-group)



[canovatesales](https://twitter.com/canovatesales)