VisionFrame[™] video monitor wall

robust video monitor wall system application engineered for unparalleled monitor support

- Assembles quickly and easily
- Integral cable management channels
- Designed to meet the specific needs of each installation
- Walls can be designed up to 13' 3" high, with limitless width
- Freestanding and Deskmount models available
- Power strips mount directly to the frame
- ETL Listed in the US and Canada



eatures

Patented VisionFrame[™] video monitor wall shall be Middle Atlantic Products model # VFMS-_(D for Deskmount, F for Freestanding). Overall Dimensions of the Video wall shall be __"W x __H" (dimensions determined by layout; not to exceed 13' 3" in height, no limit on width). Video monitor wall shall support __ 10" to 80" monitors (determined by layout) on ______ mounts (tilting, articulating). Video monitor wall shall be constructed of 3.5" x 5.25" Horizontal and 1.375" x 4.5" Vertical 6005-T5 Aluminum extrusions with internal cable management provisions. Video monitor wall shall be finished in a durable black powder coat. Mounts shall conform to the VESA FDMI standard. Freestanding video monitor wall shall be fastened to the floor and to the wall. Deskmount Video wall shall be fastened to a ViewPoint[™] Series console or LD Series LCD desk, shall be the width of the bay, and be a maximum of 80" in height. Video monitor wall shall be ETL Listed to UL Standard 962 in the US and to CAN/CSA C22.2 No. 0-M91 in Canada. Video monitor wall shall be GREENGUARD Gold Certified. Video monitor wall shall be RoHS EU Directive 2002/95/EC compliant. Video monitor wall shall be warrantied to be free from defects in material or workmanship under normal use and conditions for the lifetime of the system.

Customizable specification clips available at middleatlantic.com





US PATENT# 8, 505, 860

options:


- Three rackspace rear hanging mount shall be model # VF-VPM-3
- Accessory panel mount shall be model # VF-MPV



what great systems are built on.™

VisionFrame[™] free standing video wall basic dimensions

all dimensions in inches unless otherwise noted [all dimensions in brackets are in millimeters]





middleatlantic.com | middleatlantic.ca

VisionFrame[™] desk wall basic dimensions

all dimensions in inches unless otherwise noted [all dimensions in brackets are in millimeters]


top view






deskwall compatible with LD Series LCD desk and ViewPoint™ console (shown) in the following sizes: - 36°, 48° and 72° (ViewPoint) - 48° and 64° (LCD series desk)

front view



side view






what great systems are built on."

VisionFrame[™] monitor mounts basic dimensions

all dimensions in inches unless otherwise noted [all dimensions in brackets are in millimeters]




what great systems are built on.**

A Group brand

Middle Atlantic Products



all dimensions in inches unless otherwise noted [all dimensions in brackets are in millimeters]




NOTE: Base length is determined at time of design



what great systems are built on."

VisionFrame[™] base basic dimensions

all dimensions in inches unless otherwise noted [all dimensions in brackets are in millimeters]





what great systems are built on.™