


Rack Mount Shelves

specifications

Rack mounted shelves shall be one, two, and three rack spaces and 19 inches wide. The shelves shall be front mounted, slide-out or cantilevered versions. Keyboard shelves shall accommodate either 16.5 inch or 20 inch wide keyboards and a mouse. The keyboard shelves shall fit in a 2 RU rack space.



technical information

Rack mount shelves:	SRM19FM1:	1.7"H x 19.0"W x 15.2"D (44mm x 483mm x 385mm), 1 RU
	SRM19FM2:	3.5"H x 19.0"W x 15.2"D (88mm x 483mm x 385mm), 2 RU
	SRM19CM3:	5.2"H x 19.2"W x 12.5"D (133mm x 489mm x 316mm), 3 RU
	SRM19CMV3:	5.2"H x 19.2"W x 25.0"D (133mm x 489mm x 635mm), 3 RU
	SRM19X18A1:	1.8"H x 19.0"W x 18.0"D (44mm x 483mm x 457mm), 1 RU
	SRM19X25A1:	1.8"H x 19.0"W x 25.0"D (44mm x 483mm x 635mm), 1 RU
Shelf load rating:	SRM19FM1:	30 lbs.
	SRM19FM2:	50 lbs.
	SRM19CM3:	200 lbs.
	SRM19CMV3:	200 lbs.
	SRM19X18A1:	250 lbs.
	SRM19X25A1:	250 lbs.
	SRM19MK2:	200 lbs.; keyboards up to 16.5" wide
	SRM19MPK2:	200 lbs.; keyboards up to 20.0" wide
Keyboard shelves:	SRM19MK2:	200 lbs.; keyboards up to 16.5" wide
	SRM19MPK2:	200 lbs.; keyboards up to 20.0" wide
Keyboard shelves packaging:	Keyboard shelves come with a mouse pad, wrist pad, four standard brackets for mounting to standard channel racks, two rear support brackets for mounting to NetFrame® Racks, and #12-24 mounting screws	

key features and benefits

Center mount cantilevered shelf	Includes front and rear shelf to mount on standard 3" channel racks
Heavy load rating	Support non-rack mountable equipment up to 250 lbs.
Keyboard shelf versions include pull-out drawer with slide-out mouse tray	Storing keyboards inside of shelf when not in use make an aesthetically pleasing rack

applications

The Panduit line of shelves provide an aesthetically pleasing solution that allow you to mount test gear, computer equipment, and small networking devices on any EIA 19" rack or 23" rack with PEB1 or PEB2 extender brackets. This enables you to design a network layout to your own specifications.

When used with Panduit racks, enclosures, cable managers, and connectivity, the user receives a complete networking solution that will satisfy telecommunications room requirements today and into the future.

PANDUIT®

SPECIFICATION SHEET

Front Mount Shelves 19"

1 RU:	SRM19FM1
2 RU:	SRM19FM2

Center Mount Cantilevered Shelves, 19" 3 RU

Non-vented:	SRM19CM3
Vented:	SRM19CMV3

Adjustable Shelf 19" 1 RU

19":	SRM19X18A1
25":	SRM19X25A1

Slide-Out Keyboard/Mouse and Monitor Shelf

19":	SRM19MK2
19" pivoting:	SRM19MPK2

Racks

8' 52 RU:	CMR19x96
7' 45 RU:	CMR19x84
7' 45 RU numbers up:	CMR19x84NU
4' 24 RU:	CMR19x47
7' 45 RU 23" wide:	CMR23x84
All have #12-24 threaded rails.	

Rack Mount Shelves

front mount shelves




SRM19FM1




SRM19FM2

center mount cantilevered shelves




SRM19CM3




SRM19CMV3

slide-out keyboard shelves



SRM19MPK2



SRM19X18A1

WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT CANADA
Markham, Ontario
cs-cdn@panduit.com
Phone: 800.777.3300

PANDUIT EUROPE LTD.
London, UK
cs-emea@panduit.com
Phone: 44.20.8601.7200

PANDUIT SINGAPORE PTE. LTD.
Republic of Singapore
cs-ap@panduit.com
Phone: 65.6305.7575

PANDUIT JAPAN
Tokyo, Japan
cs-japan@panduit.com
Phone: 81.3.6863.6000

PANDUIT LATIN AMERICA
Guadalajara, Mexico
cs-la@panduit.com
Phone: 52.33.3777.6000

PANDUIT AUSTRALIA PTY. LTD.
Victoria, Australia
cs-aus@panduit.com
Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

PANDUIT[®]

For more information
Visit us at www.panduit.com
Contact Customer Service by email: cs@panduit.com
or by phone: 800.777.3300

©2014 Panduit Corp.
ALL RIGHTS RESERVED.
RKSP146--WW-ENG
Replaces WW-RKSP20
8/2014