

# AUD-1 Audio Accessory

## EXTERNAL AUDIO ADAPTER

### Product Features

- G.711 Compression
- Bidirectional Full-Duplex Audio
- Echo Cancellation
- Connects Directly to the Accessory Port
- Easy Setup
- Compact Size
- Compatible with Spectra® HD Series Dome Systems and Sarix™ Camera Models Without Built-in Audio



The **AUD-1** audio accessory is an external adapter that connects directly to the accessory port of compatible Pelco devices. The **AUD-1** is compatible with Spectra® HD Series dome systems and all Sarix™ camera models that do not have built-in audio.

The **AUD-1** audio accessory is designed to work with microphones that provide a line-level output (+4 dBu). The **AUD-1** provides 12 VDC for microphones that require it, but a preamplifier is required for microphones that require more power. The **AUD-1** encodes audio from the microphone into a digital G.711 format. The audio can be streamed with the video to be played back and recorded at the headend. The **AUD-1** can also receive the G.711 digital audio from the headend and convert it to an analog signal to be played through a speaker.

The **AUD-1** audio accessory can be used in conjunction with the ALM-1 alarm accessory. If the Pelco device has only one accessory port, a USB hub is required.

# TECHNICAL SPECIFICATIONS

## MODEL

AUD-1 External audio accessory

## GENERAL

Streaming Bidirectional: full or half duplex  
Input/Output Terminal block, analog for microphone and speaker; 600-ohm differential; 1 Vp-p maximum signal level  
Compression G.711  
Sampling Rate 8 kHz  
Bit Rate 64 kbps (8 kHz)

## ELECTRICAL

Power Input 5 VDC powered from USB

## MECHANICAL

Audio Input (microphone) UTP 600 ohm mono, 4X terminal block (screw connection), balanced line input, 12 VDC power source  
Audio Output (speaker) UTP 600 ohm mono, 2X terminal block (screw connection), balanced line output  
Connector USB 2.0 'A' male

## ENVIRONMENTAL

Operating Temperature 0° to 60°C (32° to 140°F)  
Storage Temperature -20° to 60°C (-4° to 140°F)

## PHYSICAL

Dimension 62.2 x 29.2 x 16.0 mm  
(2.45" L x 1.15" W x 0.63" H)  
Unit Weight 0.02 kg (0.04 lb)  
Shipping Weight 0.45 kg (1.0 lb)

## CERTIFICATIONS/RATINGS/PATENTS

- CE, Class A
- FCC, Class A

## SUPPLIED ACCESSORIES

USB Extension Cable Female 'A' to male 'mini-B'  
USB Extension Cable Female 'A' to custom right-angle male 'mini-B'

## SUPPORTED THIRD-PARTY MICROPHONES\*

Manufacturer	Microphones
Louroe	Verifact A, B, C, E, L-DT and K
	AOPSP-PB-F/S†
	AOP-SP-CF/CS†
	AOP-SP-WF/WS
	TLMC-W
ETC	SM1 Series

\*While many other microphones are compatible, these have been tested with the AUD-1 and are officially supported.

† Louroe AOP Series microphones may require an AOP-XD interface transceiver.

### Pelco by Schneider Electric

3500 Pelco Way, Clovis, California 93612-5699 United States

**USA & Canada** Tel (800) 289-9100 Fax (800) 289-9150

**International** Tel +1 (559) 292-1981 Fax +1 (559) 348-1120

**www.pelco.com**

Pelco, the Pelco logo, and other trademarks associated with Pelco products referred to in this publication are trademarks of Pelco, Inc. or its affiliates. All other product names and services are the property of their respective companies. Product specifications and availability are subject to change without notice. ©Copyright 2011, Pelco, Inc. All rights reserved.