

# 68A11-1

## Surveillance

### Brand Features

The Leviton Indoor/Outdoor IP Camera provides the ability to view live surveillance footage on a smartphone, tablet or the Leviton OmniTouch 7 Touchscreen when coupled with a security and automation system.

Full high definition recording at 1080p at up to 30 frames per second. The camera's built-in web server, even as a stand-alone device, allows users to view live and recorded video from a PC and have video frames sent by email or uploaded to an FTP site when motion is detected in an area. Video can also be recorded to a Micro SD card or a PC.

The high-resolution Leviton camera offers many advanced features including the capability to simultaneously dual stream H.264 and MJPEG video. For enhanced viewing capabilities, the camera automatically switches to black and white at night. The camera is suitable for outdoor use and rated IP66, featuring weatherproof housing and an operational temperature between 14 degrees Fahrenheit (F) and 122 degrees F. There is no need for power supplies or power outlets as a single Cat5 cable handles both power and communication. With the Power over Ethernet (IEEE 802.3af) feature, there is no need for power outlets, which significantly reduces the cost of cabling and installation. Additionally, its light weight and compact size offer a quick and simple installation on the ceilings or walls inside or outside of houses and buildings. After configuring its network settings, the camera can be accessed from anywhere with an Internet connection.



**UPC Code:** 87225700647

**Country of Origin:** Please Contact Customer Service

### Item Description

Indoor/ Outdoor Mini-Dome IP Camera.

### Features and Benefits

- Camera provides MJPEG real time streaming and H.264 main profile codec for a high resolution digital broadcast
- Built-in web server and network interface makes camera accessible from anywhere with a network connection
- Power over ethernet (IEEE 802.3af) feature reduces cost of cabling and installation
- Weatherproof dangle cable for outdoor use

### SPECIFICATION SUBMITTAL

<b>JOB NAME:</b> <input type="text"/>	<b>CATALOG NUMBERS:</b> <input type="text"/>	
<b>JOB NUMBER:</b> <input type="text"/>	<input type="text"/>	<input type="text"/>

#### Leviton Manufacturing Co., Inc.

201 North Service Road, Melville, NY 11747

Telephone: 1-800-323-8920 • FAX: 1-800-832-9538 • Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday): 1-800-824-3005

#### Leviton Manufacturing of Canada, Ltd.

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 • Telephone: 1-800-469-7890 •

FAX: 1-800-824-3005 • [www.leviton.com/canada](http://www.leviton.com/canada)

#### Leviton S. de R.L. de C.V.

Lago Tana 43, Mexico DF, Mexico CP 11290 • Tel.: (+52)55-5082-1040 • FAX: (+52)5386-1797 • [www.leviton.com.mx](http://www.leviton.com.mx)

**Visit our Website at:** [www.leviton.com](http://www.leviton.com)

© 2012-2015 Leviton Manufacturing Co., Inc. All rights reserved. Subject to change without notice.

#### Leviton has a global presence.

If you would like to know where your local Leviton office is located please go to: [www.leviton.com/international/contacts/](http://www.leviton.com/international/contacts/)

