

WPP-531-D-RST SPECIFICATIONS


HANDSFREE SPEAKERPHONE WITH PUSH-BUTTON AUTODIAL & RING INDICATOR BLUE STROBE LIGHT IN A WEATHERPROOF HOUSING

Distinctly noticeable blue light emergency handsfree speakerphone for both indoor and outdoor locations. Constructed with a stainless steel panel phone and a cast aluminum weatherproof black housing with TELEPHONE on door with pin latch, wall or pole mount, and flashing strobe light that will activate when phone rings. Designed to automatically dial a preprogrammed number from 1-11 digits when the button is pushed and red/green LED light provides visual indication of call progress. Capable of dialing a PBX or access number, block or allow incoming calls, and provides call duration time-out from 1-9 minutes or no time-out. Telephone can not be left off-hook, as it detects when called party hangs up and resets itself. ADA (American Disability Act) features available. Blue light option is available in a steady burning light (-SB) for location identification or a flashing blue light that activates when a call is initiated from the phone (-ST). Waterproof enclosures are offered in black, (-R) red, (-Y) Yellow, or (-G) Gray with TELEPHONE or EMERGENCY on door.









SPECIFICATIONS

Weatherproof Housing:	9 1/2"W x 19 5/8"H (Including the light) x 8"D (Including Door)
Weight:	Approximately 19 lbs.
Mounting Instructions:	Weatherproof Housing 4 holes spaced 8" x 5 7/8" Also available pole mounting bracket
Environment:	Temperature: -30°C (-22°F) to 60°C (140°F) Humidity: 0%-90% non-condensing
Programming:	Via DTMF Keypad
Input Power:	Telephone Line Powered
Loop Current:	30mA min to 80mA max
Impedance:	600 ohms
Type Jack:	RJ11C
Ringer Equivalency:	0.4A
UL & FCC Registration:	Certified
ACCESSORIES:	301-064 Security Tool (required for installation)



ADDITIONAL OPTIONS

IP - Voice over Internet Protocol Version available on all models (SIP)

-ADA	Weatherproof Housing	-ST/-SB/-RST	-RIL	-SP	Pole Mount	Additional Options & Features
						Auto Answer (AA) Remote Programming (RP) Voice Announcement (VA)
<ul style="list-style-type: none">Red/ green LED call progress indicator lightBraille Emergency Plate "EMERG. PHONE"Red push button	Standard Black & TELEPHONE on Door -B-EMER Black & EMERGENCY on Door -R Red & EMERGENCY on Door -R-TEL Red & TELEPHONE on Door -Y Yellow & EMERGENCY on Door -Y-TEL Yellow & Telephone on Door -G Grey & TELEPHONE on Door -G-EMER Grey & EMERGENCY on Door	Blue Strobe Light option: <ul style="list-style-type: none">Steady onFlashingFor location visibilityRequires AC power	Ring Indicator Light located on the phone panel for visual ring indication.	Spring loaded door option	Pole Mounting bracket fits poles 2.5" - 6".	



Providing Telecommunication Solutions Since 1930

Communication Equipment
& Engineering Company

<http://www.ceeco.net>

Email: sales@ceeco.net

519 SW Park Street

Okeechobee, FL

Voice 863-357-0798

Fax 863-357-0006