

# OUTSOURCE™

POWER OVER ETHERNET MIDSPAN INJECTOR



Compact, midspan injectors that deliver reliable POE for IP cameras and devices

Delivers enhanced POE to all 802.3af/802.3at POE and POE Plus devices. OUTSOURCE & OUTSOURCE Plus automatically detect compatible devices.

Delivers reliable remote power to IP cameras including PTZ devices

Designed for straightforward installation for high power devices

Safety assured as POE is only enabled to compliant equipment

Compact, wall-mountable unit

Integrated overload protection

Sealed, fanless design for reliability



# TECHNICAL SPECIFICATION

# OUTSOURCE™/ PLUS™

POWER		
Input Voltage	90 to 264VAC, 47 to 63Hz	
Maximum current	0.55A at 240V AC	
FORWARDED POE POWER		
OUTSOURCE	19.6 watts	(Output voltage 56V)
OUTSOURCE Plus	30 watts	(Output voltage 56V)
	Overload and short-circuit protection	
	POE output on data pairs (1 & 2, 3 & 6)	
POE STANDARDS		
OUTSOURCE	IEEE 802.3af POE	
OUTSOURCE Plus	IEEE 802.3at POE	
ETHERNET INTERFACE		
	RJ45 Data IN port	
	RJ45 Data & POE OUT port	
	10/100/1000 Base-T compatible	
LED STATUS INDICATORS		
VOR-OS	VOR-OSP	
Green blink	ON green, others off	Power on, no POE device detected
Green on	CONNECT solid green	POE detected and enabled
Green slow blink	POE PLUS blinks (others solid or off)	POE overload error
Red blink	LEDs blink (any other combination)	POE signature error
PHYSICAL / ENVIRONMENTAL		
Dimensions	L 163mm (inc mounting holes) W 65mm H 36mm	
Weight	200g [7.06oz]	
Mounting	Integral wall-mount lugs	
Operating temperature	0°C to +40°C [32°F to 104°F]	
Relative humidity	5% to 90% non-condensing	
Compliance	CE, FCC, RoHS	
PRODUCT CODES		
VOR-OS	OUTSOURCE	POE Injector
VOR-OSP	OUTSOURCE Plus	POE Plus Injector



OUTSOURCE PLUS



OUTSOURCE



veracity

## Americas & Asia Sales :

Veracity USA Inc.  
65 Harristown Road  
Suite 309  
Glen Rock  
NJ 07452  
USA  
Tel: 1-800-679-1590  
Fax: 1-800-679-0714  
[www.veracityglobal.com](http://www.veracityglobal.com)  
[sales@veracityusa.com](mailto:sales@veracityusa.com)

## EMEA Sales :

Veracity UK Ltd  
Prestwick International Aerospace Park  
4 Dow Road  
Prestwick  
KA9 2TU  
UK  
Tel +44 (0) 1292 264967  
Fax +44 (0) 845 528 1081  
[www.veracityglobal.com](http://www.veracityglobal.com)  
[sales@veracityuk.com](mailto:sales@veracityuk.com)