



DATA SHEET

Polycom Packaged Solutions

Flexible designs for advanced visual communication

Packaged solutions from Polycom are standalone units that allow you to easily bring room-based video conferencing to a variety of locations beyond the dedicated conference room. And because it's Polycom you get the same high definition meeting experience whenever and wherever you need it.

Polycom® HDX® Executive Collection floor system

The Polycom® HDX® Executive Collection floor system is an advanced solution for large meeting spaces. The freestanding video conferencing unit includes:

- Polycom® HDX® codec for industry-leading performance and quality
- Premium 50" 1080p plasma screens to showcase high definition video
- Intelligently dynamic 360 degree microphone array for finely-tuned audio

When paired with Polycom® People+Content™ collaboration technology, the HDX Executive Collection floor system allows you to easily share content from your desktop or the Internet with other conference participants.

Polycom® HDX® Media Center

The Polycom HDX Media Center is a high performance video conferencing solution for virtually any meeting space. The HDX Media Center includes:

- Polycom codec
- Audio systems including speakers
- Energy efficient ceiling or tabletop microphone arrays
- Integrated camera mounting and configurations
- Single or dual 42" displays for tabletop or wall mount, or on a pedestal
- Single 50" display for wall mount or on a pedestal

Polycom HDX Media Center displays and audio systems are tuned for Polycom codecs to provide the ultimate total conferencing experience right out of the box. The optional Polycom caster kit allows the HDX Media Center pedestal to be moved from one location to another.

Polycom Media Cart

The Polycom Media Cart is a flexible cart-only solution to fit a wide range of uses. The Media Cart has a universal mount for a single 37" to 60" display or dual 37" to 42" displays. The secure cabinet has three interior shelves for equipment, or you can choose to rack mount the equipment with the optional rack mount kit. The Polycom Media Cart is designed for even the harshest environments to give you a perfect solution for your most demanding mobile cart requirements.



Benefits

- Complete turnkey solution for simplicity of ordering, shipping, installation and service—one part number for the entire integrated system
- Sophisticated, innovative, stylish design—solutions for the boardroom, meeting room and classroom
- For mobile applications, large casters are available on select systems to share resources between multiple rooms
- Audio and video tuned to Polycom specifications to offer the best experience for users
- Global deployments unified with similar look and feel throughout an organization
- Administration and training simplified with a standard set of all A/V technology in all locations

	HDX Executive Collection	HDX Media Center	Media Cart*
Codec options available	Polycom® HDX® 8000	Polycom® HDX® 8000/7000/6000	
Screen size (min–max screen size)	Dual: 50" plasma	Single: 42" LED or 50" plasma Dual: 42" LED	Single: 37–60" Dual: 37–42"
Screen specifications	16:9 aspect ratio, 1920 x 1080 pixels	16:9 aspect ratio, 1920 x 1080 pixels	
Wall mount available		•	
Table top mount available		(for 42" configurations)	
Ceiling microphone—optional	•	•	
Caster kit		(pedestal mount only)	•
Rack mount option			•
A/V accessory storage			•
Polycom® EagleEye™ Director—optional	•	•	•
Polycom® Touch Control	•	•	•

*Monitors not included with Media Cart



Dual 42" monitor configuration
(Shown with optional caster kit)



50" Wall mount configuration



Table top media center
(Shown with HDX 6000 view media center)



Side view



Single 42" monitor configuration

Polycom HDX Media Center package includes

- Polycom® HDX® 8000/7000/6000 codec, Polycom® EagleEye™ or Polycom® EagleEye™ View camera, cables, microphone, remote control
- Dual or single 42" LED display(s) or single 50" plasma display
- Tabletop, wall or pedestal mount

Measurements, weights and electrical

- Dual 42" display unit—62 x 82 x 23" (H x W x D), 390 lbs (224 lbs wall), 5.0 A
- Single 50" display unit—62 x 42 x 23" (H x W x D), 253 lbs (227 lbs wall) , 6.5A
- Single 42" display unit (with mounting bracket)—25.7 x 39.8 x 6.3" (H x W x D), 56.92 lbs, 4.8A

Polycom HDX Executive Collection package includes

- Polycom HDX 8000 codec, Polycom EagleEye camera, cables, tabletop microphone array, and remote control
- Dual 50" 1080p plasma displays
- Pedestal mount with integrated audio system (since it includes a subwoofer)

Measurements, weights and electrical

- Dual display unit—62 x 99 x 23" (H x W x D), 278.5 lbs, 11.5A



Dual 50" monitor configuration

Polycom Media Cart package includes

- Cart with universal single VESA display mount (max VESA 600), mounting hardware, casters
- Optional: dual display kit, 19" rack mount kit, camera mount

Measurements and weights

- Single mount cart—53 x 36 x 24" (H x W x D), 126 lbs (without LCD)
- Standard VESA mounting, up to VESA 600
- Dual mount cart—55 x 79 x 24" (H x W x D), 135 lbs (without LCDs)



(Shown with optional dual display kit)

Need flexible financing?

Polycom **CAPITAL**
Collaborative Financing

www.polycom.com/polycom-capital

About Polycom

Polycom is the global leader in open standards-based unified communications and collaboration (UC&C) solutions for voice and video collaboration, trusted by more than 415,000 customers around the world. Polycom solutions are powered by the Polycom® RealPresence® Platform, comprehensive software infrastructure and rich APIs that interoperate with the broadest set of communication, business, mobile and cloud applications and devices to deliver secure face-to-face video collaboration in any environment.

Polycom, Inc.
1.800.POLYCOM
www.polycom.com

Polycom Asia Pacific Pte Ltd
+65 6389 9200
www.polycom.asia

Polycom EMEA
+44 (0)1753 723282
www.polycom.co.uk

