

# Wall-Mountable Connector Housing (WCH)

Holds 6 CCH connector panels/cassettes

CORNING

Corning wall-mountable connector housing (WCH) product family offers enhanced innovative features that make installation and troubleshooting of fiber optic connectivity faster, easier and more cost-effective. From fiber and cable routing and strain-relief to port labeling and termination, these housings reduce the risk of error that can disrupt networks.

The WCH housing provides interconnect or cross-connect capabilities between the outside plant, riser or distribution cables and the opto-electronics. With the WCH-02P (two panels, cassettes or modules), WCH-04P (four panels, cassettes or modules), and WCH-06P (six panels, cassettes or modules) capacity, the rugged metal housings can be wall mounted in main cross-connects, telecommunication rooms or other areas where space is a premium. Units accept standard closet connector housing (CCH) cassettes, connector panels and modules for a variety of connectivity options.

The WCH product family features a clear, transparent jumper side door for easy visibility during installation and testing, easy-to-use recessed mounting holes with mounting screws, documentation labels, removable strain-relief brackets, routing clips and guides, improved latches, as well as a preinstalled bubble level for simple and accurate installation. All housings also have field-installable lock kits available for both cable entry and jumper side doors.



Part Number: WCH-06P

## Features and Benefits

### Interconnect and cross-connect capabilities

Ideal for field splicing and connectorization

### Accepts CCH cassettes, panels and modules

Variety of preterminated and field-installable capabilities

### Lockable, transparent jumper side door

Visibility and ease of access for installation, testing and troubleshooting

### Removable strain-relief bracket

Flexibility for installation and moves, adds and changes (MACs)

### Segregated cable and fiber slack routing

Fiber protection

CORNING

# Wall-Mountable Connector Housing (WCH)

Holds 6 CCH connector panels/cassettes

CORNING

## Standards

### RoHS

Free of hazardous substances according to RoHS 2002/95/EG

## Specifications

### General Specifications

Application	Enterprise Networks
Mounting type	Wall-Mountable
Product Type	Wall-Mountable Hardware

### Design - Hardware

Housing Color	Black
Housing Type	WCH
Locking Availability	Provider door and jumper door
Number of Panels/Cassettes per Housing	6
Panel or Cassette Type	CCH
Splice Tray/Splice Cassette Options	Up to 6 CCH cassettes
Maximum Fiber Capacity	144

### Mechanical Characteristics

Dimensions (HxWxD)	35.8 cm x 42.2 cm x 14.5 cm (14.1 in x 16.1 in x 5.7 in)
--------------------	--

## Ordering Information

Part Number	WCH-06P
Product Description	Wall-Mountable Closet Housing (WCH), holds 6 CCH connector panels/cassettes
EAN Code	4042673245674

# Wall-Mountable Connector Housing (WCH)

Holds 6 CCH connector panels/cassettes

CORNING

## Shipping Information

Units per Delivery	1/1
Shipping Weight	5.0 kg (11.0 lb)
Package Contents	Housing; installation guide; 6 blank panels; 6 panel ID labels; hardware kit; internal strain-relief bracket; intermediate strain-relief bracket; 4 x 4-in tie wraps; 4 x 8-in tie wraps; dust brushes; 4 mounting screws; bubble level



Corning Optical Communications LLC • PO Box 489 • Hickory, NC 28603-0489 USA

800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • [www.corning.com/opcomm](http://www.corning.com/opcomm)

A complete listing of the trademarks of Corning Optical Communications is available at [www.corning.com/opcomm/trademarks](http://www.corning.com/opcomm/trademarks). All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2014 Corning Optical Communications. All rights reserved.

CORNING