

NetCommander 16-Port Cat5 KVM Switch 1U Rack-Mount with PS2 to USB Input Adapter

MODEL NUMBER: **B072-016-1A**



Description

Tripp Lite's 16-Port NetCommander 1U Rackmount Cat5 KVM Switch with PS2/USB adapter, is the next generation of our cost-effective, feature rich, KVM switches. It's sleek, 1U design and compact size, features RJ45 connection ports that utilize inexpensive Cat5 patch cables, reducing the amount of cable clutter normally found with traditional KVM cabling. Easily switch between CPU's with Push Buttons, Hot-Key commands, or built-in On Screen Display (OSD) menu function. Cascadability allows connection to up to 256 computers. Compatible with PS/2 and USB computers, VGA, SVGA, or XGA monitors, as well as all major operating systems. On board PS/2 connections for Keyboard / Mouse, or use included adapter to convert to USB Keyboard / Mouse ports. Constructed of heavy-duty steel housing.

Features

- Expandable - Cascade a second level of KVM switches to control up to 256 servers from a single station
- Extend distance: between computer and switch up to 30 meters/100 ft.
- Rack mountable: sleek, 1U space saving KVM switches
- Accepts PS2 Mouse and Keyboard (or USB Mouse and Keyboard with included adapter)
- Innovative CAT5 technology: eliminate cable clutter at the rack
- Multi-layer security: protects your corporate data
- Easy server management: choice of On Screen Display, Hot-key, or push button control
- Multi-platform: PS/2 and USB support
- Easily add IP functionality with Tripp Lite Model [B051-000](#)
- Add Tripp Lite Model [B021-000-19](#) for space saving, in-the-rack, LCD, Keyboard and Mouse
- Compact Size: 17"W x 5"D x 1.75"H
- Video Resolution: 1600x1200@75Hz
- Internal Power Supply
- Compatible with all major operating systems
- Constructed of heavy-duty steel housing

Highlights

- 16 RJ45 Ports utilize inexpensive Cat5 patch cables
- Accepts PS2 or USB Mouse and Keyboards with included Adapter
- Expandable - Cascade a second level of KVM switches to control up to 256 servers from a single station

System Requirements

- Computers: The Tripp Lite [B078-101-PS2](#), or [B078-101-USB-1](#) Server Interface Module must be used to connect a server to the server ports on the KVM switch.
- Compatible with all major operating systems

Package Includes

- 16-Port NetCommander 1U Rackmount Cat5 KVM Switch
- PS2 to USB Adapter
- 6ft Power Cord
- 6ft Firmware Upgrade Cable
- Rackmount Bracket kit



Specifications

OVERVIEW	
Users	1
Port Control	Push Buttons, Hotkeys, OSD
Max CPU	256
PC/Server Connections	PS/2; USB; VGA
Cat5 KVM Switch	Yes
IP Remote Access	No
Style	1U Rackmount
PHYSICAL	
Color	Black
ENVIRONMENTAL	
BTUs	27.296
CONNECTIONS	
Connector A	HD15 (FEMALE)
Connector B	MINI DIN-6 (FEMALE) (X2)
Ports	16
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.