

4-Port Plug-n-Play USB 2.0 over Cat5/Cat6 Extender Hub, Transmitter and Receiver, Hi-Speed USB up to 164-ft. (50M)

MODEL NUMBER: **B203-104-PNP**



Description

Tripp Lite's High Speed Plug and Play USB 2.0 over Cat5 Extender Kit with 4-Port Hub allows placement of USB hub up to 50 meters (164ft) away from a source computer. Using solid conductor Cat5e rated cable, a full 480mbps transmission speed is maintained over the entire distance. Ideal for any situation where up to four USB devices need to be located more than the maximum 5-meter distance allowed by the USB timing signal. Also see B203-101-PNP for single device extension. For Solid Conductor patch cables, see Tripp Lite N202- series patch cables. Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

Features

- Kit includes Transmitter and 4port Hub Receiver
- Up to 50 meters (164ft) distance over Solid Conductor Cat5e/Cat6 cable
- Supports high speed data transfer rates up to 480mbps
- Plug and Play...no Drivers or Software required
- Backwards compatible to USB 1.1
- Windows and MAC compatible
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

OVERVIEW	
Chromebook Compatible	Yes
Style	USB

Highlights

- High Speed USB 2.0 over Cat5 4-port Hub Kit
- Up to 50 meters away from USB source
- Plug and Play...no Drivers or Software required
- Windows and MAC compatible
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Applications

- Use with USB 2.0 peripherals that need to exceed the 16 ft. (5M) distance limitation

Package Includes

- Local transmitter unit
- Remote 4-port receiver unit
- External power supply (Input: 100-240V, 50/60Hz, 0.5A Output: 5V, 2A)
- Owner's manual



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

PHYSICAL	
Color	Black
ENVIRONMENTAL	
Operating Temperature Range	0 to 40 C (32 to 104 F)
Storage Temperature Range	-20 to 60 C (-4 to 140 F)
Relative Humidity	20 to 90%
CONNECTIONS	
Connector A	RJ45 (FEMALE) (X2)
Connector B	USB A (FEMALE) (X4)
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.