

## Full-Motion Wall-Mount for 13" to 27" Flat-Screen Displays

MODEL NUMBER: **DWM1323SE**



### Description

Tripp Lite's VESA-compliant DWM1323SE Tilt Flat-Screen Wall Mount offers full-motion articulation and can free up valuable space in your workstation by allowing you to effortlessly re-position your display at any time, even after installation. Its sleek design features convenient one-touch swivel display adjustment with tilt capabilities and fits most 13- to 27-inch flat-panel displays. Its durable, all-metal frame with scratch-resistant, powder-coat finish withstands the stress of repeated use and blends easily into any décor. It comes with all necessary mounting hardware and supports weights of up to 33 lb. For peace of mind, the DWM1323SE comes backed by a 5-year warranty and green, RoHS-compliant design.

### Features

- Tripp Lite's VESA-compliant DWM1323SE Tilt Flat-Screen Wall Mount offers full-motion articulation and can free up valuable space in your workstation by allowing you to effortlessly re-position your display at any time, even after installation
- Sleek design features convenient one-touch swivel display adjustment with tilt capabilities
- Fits most 13- to 27-inch flat-panel displays
- Durable, all-metal frame with scratch-resistant, powder-coat finish withstands the stress of repeated use and blends easily into any décor
- Includes all necessary mounting hardware and supports weights of up to 33 lb
- 5-year warranty
- Green, RoHS-compliant design

### Highlights

- **SEE NEW MODEL - DWM1327SE**
- Can be used to increase available desk/table space in office applications
- Fits most flat-panel displays from 13" to 27"
- Convenient one-touch swivel display adjustment for easy view optimization (tilt is adjustable with included Allen wrench)
- Wide range of motion with -15° to +15° tilt and 180° swivel capability
- Supports up to 33 lbs.
- 5-year warranty

### Package Includes

- DWM1323SE Full Motion Flat-Screen Wall Mount
- Mounting Hardware
- Owner's Manual

## Specifications

OVERVIEW	
Mounting Location	Wall
PHYSICAL	



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Unit Weight (lbs.)	2.66
Unit Weight (kg)	1.26
Color	Black
Monitor Display Size (in.)	13 - 27
Monitor Display Size (cm)	33.02 - 68.58
VESA Pattern (mm)	75x75; 100x100
Motion	Full
Degrees of Motion	-15/+15 Tilt; 180 swivel
Min/Max Arm Extension (in.)	4.14 min to 15.95 max
Min/Max Arm Extension (cm)	10.5 min to 40 max
Maximum Weight Capacity (lbs.)	33
Maximum Weight Capacity (kg)	15
<b>FEATURES &amp; SPECIFICATIONS</b>	
Tools Necessary	Yes
Cord Management	No
<b>WARRANTY</b>	
Product Warranty Period (U.S. & Canada)	5-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.