



Tilt Wall-Mount for 26" to 55" Flat-Screen Displays

MODEL NUMBER: DWT2655XP



Description

Tripp Lite's VESA-compliant DWT2655XP Tilt Flat-Screen Wall Mount's low-profile design features an open frame for easy wall access and optimal display positioning flexibility. With tilt adjustment for improved viewing angles in applications where the audience is located below the display, it packs a lot of functionality into an unobtrusive frame. It can also free up valuable space in your workstation by allowing you to effortlessly reposition your display at any time, even after installation. Its durable, all-metal construction with scratch-resistant, powder-coat finish supports weights of up to 165 lbs. and fits most 26- to 55-inch flat-panel displays. It comes with all necessary mounting hardware and features horizontal adjustment to compensate for off-center wall studs. A built-in bubble level enables accurate display leveling. For peace of mind, the DWT2655XP comes backed by a 5-year warranty and green, RoHS-compliant design.

Highlights

- **REPLACES DWT2647XP**
- Low-profile mounting keeps unit out of sight for sleek, professional appearance Fits most flat-panel displays from 26" to 55"
- Open frame for easy wall access
- Tilt adjustment improves viewing angles in applications where the audience is below the display
- Horizontal adjustment compensates for off-center wall studs
- Wide range of motion with -10° to +10° tilt capability
- Equipped with a bubble level for accurate display leveling
- Supports up to 165 lb
- 5-year warranty

Package Includes

- DWT2655XP Tilt Flat-Screen Wall Mount
- Mounting Hardware
- Owner's Manual

Specifications

OVERVIEW	
Mounting Location	Wall
PHYSICAL	
Unit Weight (lbs.)	6.78
Unit Weight (kg)	3.07
Color	Black
Monitor Display Size (in.)	26 - 55
Monitor Display Size (cm)	66.04 - 139.70
VESA Pattern (mm)	200x200; 300x300; 400x200; 400x400
Motion	Tilt



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Degrees of Motion	-10/+10 Tilt
Min/Max Arm Extension (in.)	N/A
Min/Max Arm Extension (cm)	N/A
Maximum Weight Capacity (lbs.)	165
Maximum Weight Capacity (kg)	75
FEATURES & SPECIFICATIONS	
Tools Necessary	Yes
Cord Management	No
WARRANTY	
Product Warranty Period (U.S. & Canada)	5-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.