




# DIRECT CONNECT & PRISON PHONES

## 350 STAINLESS STEEL PANEL TELEPHONES

CEEEO's extensive line of prison visitation phones offer reliable communication for prison visitation areas, dormitories, control rooms, sallyports, gates and entryways. The SSP-350 telephone is constructed of stainless steel, equipped with a 32" armored cord handset, and mounted in standard 4" gang box, double gang or double gang wall mount. Units are available with stationary cradle or operable sealed hookswitch. All CEEEO telephones carry a one year warranty; however, CEEEO guarantees service for the life of the product!

### SPECIFICATIONS

<b>Panel Size:</b>	5" W x 5" H 3.12" D (Front Panel & Handset on Hook)
<b>Weight:</b>	Approximately 3 lbs.
<b>Mounting :</b>	Flush mount- <b>(Standard)</b> 4" mounting electric box Dimensions: 4"x 4" x 2.12"D Double gang wall mount <b>(-W)</b> Dimensions: 4.56"x 4.62" x 2"D
<b>Environment:</b>	Temperature: -30°C (-22°F) to 60°C (140°F) Humidity: 0%-90% non-condensating
<b>Input Power:</b>	Telephone Line Powered
<b>Loop Current:</b>	23mA min to 80mA max
<b>Impedance:</b>	600 ohms
<b>Type Jack:</b>	RJ11C
<b>Ringer Equivalency:</b>	0.4A
<b>Hearing Aid Compatible:</b>	Meets EIA standards
<b>UL&amp; FCC Registration:</b>	Certified
<b>ACCESSORIES:</b>	301-064 Security Tool (required for installation)







CEEEO has been providing telecom solutions since 1930. Our vandal resistant technology focuses on providing public communication solutions while reducing replacement and repair costs, lowering the customer's total cost of ownership. CEEEO also offers custom design and branding to your specifications. Our commitment to providing expert service and support extends beyond the warranty of our product. *We offer support for the life of the product!* CEEEO is devoted to giving you the quality and service you deserve.






# DIRECT CONNECT & PRISON PHONES

## 350 STAINLESS STEEL PANEL TELEPHONES





Stainless Steel direct connect & prison visitation phones

SSP-350-X	SSP-350D-X-M	SSP-350-X-M-STC	SSP-350-X-M-2ACH
 (Dukane & Rauland Compatible)		 (Dukane & Rauland Compatible)	
<b>Dimensions:</b> 5"H x 5"W	<b>Dimensions:</b> 4 1/2"H x 4 1/2"W	<b>Dimensions:</b> 4 1/2"H x 4 1/2"W	<b>Dimensions:</b> 5"H x 5"W
<p><b>SSP-350-X Model</b> Stainless Steel, Direct Connect communication 4" mounting electrical box (two typically required) Chrome Hookswitch and Cradle 32" Armored Cord Handset • Optional cord lengths Tamper Resistant Security Screws <b>Ring-down Operation (X)</b></p> <p><b>SSP-350-X-M Model</b> <b>Magnetic Hookswitch (M)</b> • Completely sealed • Activated When the Handset is Lifted</p> <p><b>SSP-350-X-M-LB Model</b> <b>Lanyard Bracket (LB)</b> • Internal steel lanyard</p>	<p><b>SSP-350D-X-M-W Model</b> Stainless Steel, Direct Connect Communication 4" mounting electrical box (two typically required) 32" Armored Cord Handset • Optional cord lengths Tamper Resistant Security Screws <b>Ring-down Operation (X)</b> <b>Magnetic Hookswitch (M)</b> • Completely sealed <b>2-gang Style Faceplate (2G)</b> <b>Wall Mounted Box (WB)</b></p> <p><b>SSP-350D-X-M-RG-RIL-W</b> <b>Ringer (RNG)</b> <b>Wall Mounted Box (W)</b> <b>Ring Indicator Light (RIL)</b></p>	<p><b>SSP-350-X-M Model</b> Stainless Steel, Direct Connect Communication 4" mounting electrical box (two typically required) 32" Armored Cord Handset • Optional cord lengths Tamper Resistant Security Screws <b>Magnetic Hookswitch (M)</b> • Activated When the Handset is Lifted <b>Screw Terminal Connection (STC)</b></p> <p><b>SSP-350-X-M-STC</b> <b>Magnetic Hookswitch (M)</b> <b>Screw Terminal Connection (STC)</b></p>	<p><b>SSP-350-X-M-RG Model</b> Stainless Steel, Direct Connect Communication 4" mounting electrical box (two typically required) 32" Armored Cord Handset • Optional cord lengths Tamper Resistant Security Screws Activated When the Handset is Lifted <b>Magnetic Hookswitch (M)</b> • Completely sealed • Activated When the Handset is Lifted <b>Ringer (RNG)</b></p> <p><b>SSP-350-X-M-2ACH Model</b> <b>Magnetic Hookswitch (M)</b> • Completely sealed • Activated When the Handset is Lifted <b>Two 32" Armored Cord Handsets (2ACH)</b></p>

**ADDITIONAL OPTIONS** IP - Voice over Internet Protocol Version available on all models (SIP)

-M	-LB	-PBVC	-RIL	-W
				
<b>Sealed Magnetic Hookswitch</b> • Completely Sealed • No Moving Parts	32" handset with internal steel lanyard (braided metal rope) anchored into bracket installed on panel for added strength	Push button volume control handset	Ring indicator light that is mounted on top of the phone	2-gang style grey metal surface wall mounted box Dimensions: 4.56" x 4.62" x 2"D

**POWER SYSTEM FOR PRISON VISITATION STATIONS**

 Power Supply Interface (1 Pair)	 Power Supply for up to 6-8 pair	 Prison Control System for up to 16 pair	 Power Supply for one set of prison visitation phones
<b>350-250 (shown)</b>	<b>350-255 (shown)</b>	<b>350-300 (shown)</b>	<b>350-220 (shown)</b>
<b>350-250:</b> 2 Way Interface <b>350-253:</b> 3 Way Interface	<b>350-255:</b> 6-8 pair Power Supply	<b>350-300:</b> Power & Connection 16 pair <b>350-300R:</b> Power & connection with recorder interface, 16 pair	<b>350-220:</b> Manual Ring-Down Circuit with Power Supply for 1 pair