

# SSP-560-F SPECIFICATIONS



## LARGE FLUSH OR WALL MOUNTED HANDSFREE SPEAKERPHONE WITH KEYPAD FOR LOW POWER CONSUMPTION




Robust heavy gauge stainless steel flush mount or surface mount low power consumption handsfree speakerphone with keypad for standard dialing, push button for dial tone, and red LED light to indicate phone is activated. Press to start/press to stop button for initiation and termination of phone calls. Telephone can be programmed to cancel calls after 1, 3, or 5 minutes or no time out. Built with marine quality chrome tone dial keypad, instruction or advertising window, weatherproof, puncture resistant speaker and microphone, and tamper resistant security screws. Optional (-SW) stainless steel surface mount box available.



### SPECIFICATIONS

<b>Panel Size:</b>	10.12"W x 13.12"H 2"D (Behind Panel) 2.65"D (With Wall Mounting Box)
<b>Weight:</b>	Approximately 6 lbs.
<b>Mounting Instructions:</b>	Rough-in flush mounting box <b>(Standard)</b> Dimensions: 8.50" W x 11.50"H x 2.75" D 3 mounting holes per side of panel spaced 5.25" apart vertically and two holes spaced 7.8" apart horizontally Surface Wall Mounting Box <b>(-SW)</b> 4 holes spaced 6W" x 9H"
<b>Environment:</b>	Temperature: -30°C (-22°F) to 60°C (140°F) Humidity: 0%-90% non-condensating
<b>Programming:</b>	Via Keypad
<b>Input Power:</b>	Telephone Line Powered
<b>Loop Current:</b>	27mA min to 80mA max
<b>Impedance:</b>	600 ohms
<b>Type Jack:</b>	RJ11C
<b>Ringer Equivalency:</b>	0.4A
<b>UL &amp; FCC Registration:</b>	Certified
<b>ACCESSORIES:</b>	301-037 Security Tool (required for installation When in a Box)



ADDITIONAL OPTIONS		IP - Voice over Internet Protocol Version available on all models (SIP)	
-SW	-RIL	Standard rough in mounting box	Additional Options & Features
			Auto Answer (AA) Remote Programming (RP) Voice Announcement (VA)
Stainless steel wall/surface mounting box	Ring Indicator Light located on the phone panel for visual ring indication.	Rough-in flush mounting box Dimensions: 8.50" W x 11.50"H x 2.75" D	



*Providing Telecommunication Solutions Since 1930*

Communication Equipment  
& Engineering Company

<http://www.ceeco.net>  
Email: [sales@ceeco.net](mailto:sales@ceeco.net)

519 SW Park Street

Okeechobee, FL

Voice 863-357-0798

Fax 863-357-0006