

Cat6 Gigabit Bulk Solid PVC Cable - Gray, 1000-ft.

MODEL NUMBER: N222-01K-GY



Description

With Tripp Lite's new category 6 bulk solid PVC cable you can stay ahead of the game with use of this high-speed cabling to distribute data voice and video. These cables deliver stable performance up to 550MHz. Each comes UL verified meets EIA/TIA, Cat6, TIA/EIA 568-b-2.1 draft 9 standards. Constructed with high-quality copper wire, near-end crosstalk levels are kept to a minimum. This 1000-ft. spool of bulk solid PVC cable makes industrial runs a snap. Cat6 cables are available in a variety of colors and sizes.

Features

- Designed for premise (in-wall) cabling applications
- Meets category 6 cabling standards
- Premium cabling for category 6, category 5e and category 5 applications
- Drastically reduce impedance and structural return loss compared to standard 100MHz wire
- High-quality copper wire
- Length: 1000-ft. Color: gray
- 24 AWG 4-pair solid cable with PVC (CMR) jacket
- Deliver stable performance up to 550MHz/ 1 Gbps communication
- Meets most current industry standards including IEEE 802.3ab, IEEE 802.5, ANSI/EIA/TIA 568, ISO/IEC 11801 and ETL (category 6 draft 11)
- Available in plenum cable (N224-01K-GY)

Highlights

- Meets category 6 cabling standards
- Drastically reduce impedance and structural return loss compared to standard 100Mhz wire
- 4pr Solid Conductor - CMR PVC Jacket

System Requirements

- For 1000 Base-T (1Gbps Ethernet), 10/100 Base-T (Ethernet), 100 Mbps TPDDI, 155 Mbps ATM, ISDN, voice and Token Ring TYPE 3 applications as well as EIA/TIA applications

Package Includes

- 1000-ft. Cat6 Gigabit Bulk Solid Gray PVC Cable

Specifications

OVERVIEW	
Style	Bulk Spooled PVC
Model Type	Bulk Cables
Cable Types	CAT6



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

INPUT	
Cable Length (ft.)	1000
Cable Length (m)	304.80
PHYSICAL	
Color	Gray
CERTIFICATIONS	
Approvals	UL verified, meets EIA/TIA CAT6 TIA/EIA- 568-B-2.1, DRAFT 9 standards
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.