

## Duplex Multimode 62.5/125 Fiber Patch Cable (LC/ST), 2M (6-ft.)

MODEL NUMBER: **N318-02M**



### Highlights

- Manufactured from 62.5/125 duplex (zipcord) fiber
- Ideal for LAN applications
- Glass fiber composition

### System Requirements

- Any fiber optic hardware or NIC card requiring multimode duplex cable with ST/LC connectors

### Package Includes

- 2-meter duplex MMF LC/ST 62.5/125 fiber cable

### Description

Tripp Lite's 2-meter multimode duplex fiber optic ST/LC patch cable is manufactured from 62.5/125 zipcord fiber. The cable has LC to ST connectors, a PVC jacket and is FDDI and OFNR rated. Duplex multimode fiber is most commonly used in LAN applications.

### Features

- Manufactured from 62.5/125 duplex (zipcord) fiber
- PVC jacket
- Length: 2-meter/Connectors: 2 ST/LC connectors on each end
- Insertion loss testing performed on every connector (0.2db typical) and provided with cable
- Beveled edge on ends of glass makes insertion of plug a breeze
- Fiber made from glass (not a polymer)
- Duplex multimode fiber is most commonly used in LAN applications where links are 10 feet or less
- Fiber optic distributed data interface (FDDI) rated
- OFNR (riser rated)

## Specifications

| OVERVIEW      |                                |
|---------------|--------------------------------|
| Network Speed | 1Gbps                          |
| Style         | Fiber Optic                    |
| Fiber Type    | 62.5/125 - OM1                 |
| Model Type    | LC/ST                          |
| Cable Types   | MULTIMODE 62.5/125 FIBER OPTIC |



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

| INPUT                               |                           |
|-------------------------------------|---------------------------|
| Cable Length (ft.)                  | 7                         |
| Cable Length (m)                    | 2                         |
| PHYSICAL                            |                           |
| Color                               | Orange                    |
| CONNECTIONS                         |                           |
| Connector A                         | LC                        |
| Connector B                         | ST                        |
| Connector C                         | LC                        |
| Connector D                         | ST                        |
| Number of Connectors                | 4                         |
| CERTIFICATIONS                      |                           |
| Certifications                      | ROHS                      |
| WARRANTY                            |                           |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.