

## Access IT Centralized Remote Access Management

MODEL NUMBER: 0SU00018



### Description

#### Solving the need to manage remote access

In today's complex corporate environments, IT managers are charged with managing remote server rooms and distributed IT assets at a "click's length," so that every problem is dealt with in real-time, or even better, prevented through ongoing maintenance. This calls for a secure, simple, yet cost-effective solution to manage today's ever-growing list of remote access connections and protocols.

#### Enhancing the level of IT service

AccessIT is a secure web-based, centralized remote access management solution that enhances IT efficiency and productivity. AccessIT consolidates all remote access services into a single session, providing IT staff with critical on-demand remote access to all IT assets, regardless of their physical location.

AccessIT is targeted at mid-sized organizations, allowing for the connection of up to 250 targets, and providing access to up to 10 IT personnel that are in charge of the daily management, maintenance, monitoring and control of the company's mission critical IT assets. AccessIT Enterprise Edition is designed for larger organizations, and supports up to 1000 targets, and more than 20 users.

#### Providing the Real Needs of IT

Its unique, open platform architecture provides a single portal to access and control ALL IT hardware (servers, console servers, PDUs, etc.) regardless of manufacturer. By embracing IT products from a wide range of vendors, AccessIT enables organizations to leverage their existing IT equipment, knowledge, and training.

### Features

- AccessIT allows for the connection of up to 250 targets, and provides access to up to 10 users
- Integrates in-band and out-of-band access
- Combines access and power

### Highlights

- AccessIT allows for the connection of up to 250 targets, and provides access to up to 10 users
- Integrates in-band and out-of-band access
- Combines access and power
- Manages access & control of heterogeneous environments
- Maximizes tools that have already been deployed
- Overcomes implementation challenges
- Increases operational efficiency while maintaining security
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

### Package Includes

- AccessIT Manager Appliance
- Rackmount kit



- Manages access & control of heterogeneous environments
- Maximizes tools that have already been deployed
- Overcomes implementation challenges
- Increases operational efficiency while maintaining security
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

## Specifications

OVERVIEW	
Model Type	IP Remote Units
Accessories Type	Remote Management
PHYSICAL	
Unit Dimensions (hwd / in.)	1.7 x 17.2 x 9.8
Unit Dimensions (hwd / cm)	4.32 x 43.7 x 24.9
Unit Weight (lbs.)	9.9
Unit Weight (kg)	4.5
ENVIRONMENTAL	
Storage Temperature Range	-20 to 80 C
Relative Humidity	5 to 95%, Non-Condensing
Operating Temperature	0 to 40 C
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.