

External 192V Tower Battery Pack for select Tripp Lite UPS Systems (BP192V1407C-1PH)

MODEL NUMBER: **BP192V1407C-1PH**



Highlights

- Extends runtime of compatible Tripp Lite UPS Systems using 192VDC configuration
- Includes built-in 7A charger
- Includes UPS connection cabling
- 10 year design life
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Description

Tripp Lite's BP192V1407C-1PH External Battery Pack with built-in 7A charger offers extended battery runtime when used in conjunction with compatible Tripp Lite UPS systems. Includes heavy gauge cabling to connect to host UPS. Multiple BP192V1407C-1PH batteries can be daisy-chained for longer runtime configurations with appropriate contractor-supplied battery pack interconnection cabling (see manual). Internal battery charger is powered via hardwire connection to 120V 30A electrical service.

COMPATIBLE UPS SYSTEMS: SU5000RT4U, SU6000RT4U, SU8000RT4U and other Tripp Lite UPS systems specifying the use of this battery pack.

Features

- Offers extended-run UPS operation when used in conjunction with compatible Tripp Lite UPS systems
- 10 year design life
- Multiple battery packs can be daisy-chained through each other to the UPS for even longer extended run operation
- Cabling to connect one BP192V1407C-1PH is included - cabling for additional battery packs is contractor supplied
- Includes built-in 7A charger powered via hardwire 120VAC 30A input connection

Specifications

BATTERY	
Expandable Battery Runtime	Multiple battery packs can be daisy-chained to the UPS for extended runtime. Configuration specific cabling for multi-battery pack configurations is contractor provided.
DC System Voltage (VDC)	192
UPS Connection	Included cabling enables connection between unique UPS connector and hardwire DC terminals in battery pack. Cabling to connect multiple external battery packs is contractor provided.
PHYSICAL	
Shipping Dimensions (hwd / in.)	63 x 37 x 36



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Shipping Dimensions (hwd / cm)	160 x 94 x 91.4
Shipping Weight (lbs.)	2140
Shipping Weight (kg)	971.6
Unit Dimensions (hwd / in.)	60 x 32.4 x 28.8
Unit Dimensions (hwd / cm)	152.4 x 82.3 x 73.2
Unit Weight (lbs.)	2070
Unit Weight (kg)	939.8
Material of Construction	Steel
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.