

The display you are connecting must have a HDMI port that can accept a converted HDMI signal. Contact your display manufacturer to confirm that it will work with a VGA + Audio to HDMI converter. If your display does not support this, an alternative solution is Tripp Lite's (Model: Number: U244-001-HDMI-R) USB to HDMI adapter.

VGA with Audio to HDMI Converter, Adapter for Stereo Audio and Video

MODEL NUMBER: **P116-000-HDMI**



Description

Tripp Lite's P116-000-HDMI VGA + Audio to HDMI converter is the perfect solution for using your older laptop or PC with your new HDMI display. Simply connect your computers VGA and Audio ports to the converter, and the converter to the HDMI port on your display, and you are ready to go. No software or drivers required. If your computer has only a 3.5 mm. Mini Stereo Audio jack, connect it to the converter using a 3.5 mm. to RCA adapter cable such as Tripp Lite's [P314-006](#). You can also convert the RGB Video and Stereo Audio signals on your DVD player, DVR, etc., for use on your HDMI display (Component Video to VGA adapter required) Furthermore, you reduce your equipment costs by eliminating the need to upgrade your computer's video card.

The P116-000-HDMI supports HD video resolutions up to 1080p, and computer video resolutions up to 1280 x 1024. Supports 24-bit True Color (8-bits per channel), and HDCP compliant.

Features

- Connect your VGA laptop or PC to a HDMI display to enjoy high definition video and audio
- Convert the RGB Video and Stereo Audio signals from your DVD player, DVR, etc., for use on a HDMI display (Component Video to VGA adapter required)
- Plug-and-Play, no software or drivers required
- Supports HD video resolutions up to 1080p, and computer video resolutions up to 1280 x 1024
- Supports 24-bit True Color (8-bits per channel)
- Reduce equipment cost by eliminating the need to update your computer's video card
- HDCP compliant

Specifications

Highlights

- Connect your VGA laptop or PC to a HDMI display to enjoy high definition video and audio
- Convert the RGB Video and Stereo Audio signals from your DVD player, DVR, etc., for use on a HDMI display (Component Video to VGA adapter required)
- Plug-and-Play, no software or drivers required
- Supports HD video resolutions up to 1080p, and computer video resolutions up to 1280 x 1024
- Reduce equipment cost by eliminating the need to update your computer's video card
- HDCP compliant

System Requirements

- The display you are connecting must have a HDMI port that can accept a converted HDMI signal. Contact your display manufacturer to confirm that it will work with a VGA + Audio to HDMI converter. If your display does not support this, an alternative solution is Tripp Lite's [U244-001-VGA-USB](#) to HDMI adapter.
- Computer with a VGA Video and 3.5 mm. or RCA Audio Jacks (If your computer has only a 3.5 mm. Mini Stereo Audio jack, you can use a 3.5 mm. to RCA adapter cable such as Tripp Lite's [P314-006](#).
- DVD player, DVR, etc. with RGB Video and Stereo Audio jacks (Component video to VGA adapter required)
- **Supported PC Video Resolutions** - 640 x 480 @ 60Hz, 72Hz, 75Hz, 85Hz, 800 x



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.triplite.com

OVERVIEW	
Chromebook Compatible	No
Display Style	Adapter
Model Type	VGA
Cable Types	VGA
PHYSICAL	
Shipping Dimensions (hwd / in.)	2.1 x 8.1 x 5.7
Shipping Weight (lbs.)	1.1
Unit Dimensions (hwd / in.)	1.25 x 3.5 x 2.75
Unit Weight (lbs.)	0.4
Color	Black
ENVIRONMENTAL	
Operating Temperature Range	5 to 131 F (-15 to 55 C)
Relative Humidity	5 to 90% RH, Non-Condensing
CONNECTIONS	
Connector A	HD15 (FEMALE) & RCA (FEMALE) (X2)
Connector B	HDMI (FEMALE)
Connector C	HDMI (FEMALE)
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

600i @ 60Hz, 1280 x 800 @ 60Hz, 1280 x 600 @ 56Hz, 60Hz, 72Hz, 75Hz, 85Hz, 1024 x 768 @ 60Hz, 70Hz, 75Hz, 80Hz, 85Hz, 1280 x 1024 @ 60Hz, 75Hz

- **Supported HD Video**

Resolutions - 480i @ 60Hz, 480p @ 60Hz, 720p @ 60Hz, 1080i @ 60Hz, 1080p @ 60Hz

Package Includes

- P116-000-HDMI VGA + Audio to HDMI Converter
- 4.9 ft. External Power Supply (Input: 100-240V, 50/60Hz, 0.5A Output: 5V, 1.2A)
- Owner's Manual

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.