


Fixed Wall-Mount for 32" to 70" Flat-Screen Displays

MODEL NUMBER: **DWF3260X**



Description

Tripp Lite's VESA-compliant DWF3260X Fixed Flat-Screen Wall Mount's low-profile design features an open frame for easy wall access and optimal display positioning flexibility. Its durable, all-metal construction with scratch-resistant, powder-coat finish supports weights of up to 165 lbs. and fits most 32- to 70-inch flat-panel displays. It comes with all necessary mounting hardware and features horizontal adjustment to compensate for off-center wall studs. A built-in bubble level enables accurate display leveling. For peace of mind, the DWF3260X comes backed by a 5-year warranty and green, RoHS-compliant design.

Features

- Low-profile design features an open frame for easy wall access and optimal display positioning flexibility
- Durable, all-metal construction with scratch-resistant, powder-coat finish supports weights of up to 165 lbs. and fits most 32- to 70-inch flat-panel displays
- Includes all necessary mounting hardware and features horizontal adjustment to compensate for off-center wall studs
- Built-in bubble level enables accurate display leveling
- 5-year warranty and green
- RoHS-compliant design

Highlights

- **SEE NEW MODEL - DWF3270X**
- Low-profile mounting keeps unit out of sight for sleek, professional appearance
- Fits most flat-panel displays from 32" to 70"
- Open frame for easy wall access
- Horizontal adjustment compensates for off-center wall studs
- Equipped with a bubble level for accurate display leveling
- Supports up to 165 lbs.
- 5-year warranty

Package Includes

- DWF3260X Fixed Flat-Screen Wall Mount
- Mounting Hardware
- Owner's Manual

Specifications

OVERVIEW	
Mounting Location	Wall
PHYSICAL	
Unit Weight (lbs.)	5.19
Unit Weight (kg)	2.35
Color	Black



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Monitor Display Size (in.)	32 - 70
Monitor Display Size (cm)	81.28 - 177.80
VESA Pattern (mm)	600x400
Motion	Fixed
Min/Max Arm Extension (in.)	N/A
Min/Max Arm Extension (cm)	N/A
Maximum Weight Capacity (lbs.)	165
Maximum Weight Capacity (kg)	75
FEATURES & SPECIFICATIONS	
Tools Necessary	Yes
Cord Management	No
WARRANTY	
Product Warranty Period (U.S. & Canada)	5-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.