

Tilt Wall-Mount for 13" to 27" Flat-Screen Displays

MODEL NUMBER: **DWT1323S**



Description

Tripp Lite's VESA-compliant DWT1323S Tilt Flat-Screen Wall Mount's low-profile design stays hidden behind your display for a sleek, professional appearance. With tilt adjustment for improved viewing angles in applications where the audience is located below the display, it packs a lot of functionality into a compact frame. It can also free up valuable space in your workstation by allowing you to effortlessly reposition your display at any time, even after installation. Its durable, all-metal construction with scratch-resistant, powder-coat finish supports weights of up to 88 lbs. and fits most 13- to 27-inch flat-panel displays. It comes preassembled for quick and easy installation and features horizontal adjustment to compensate for off-center wall studs. For peace of mind, the DWT1323S comes backed by a 5-year warranty and green, RoHS-compliant design.

Features

- Tripp Lite's VESA-compliant DWT1323S Tilt Flat-Screen Wall Mount's low-profile design stays hidden behind your display for a sleek, professional appearance
- Tilt adjustment improves viewing angles in applications where the audience is located below the display
- It can also free up valuable space in your workstation by allowing you to effortlessly reposition your display at any time, even after installation
- Durable, all-metal construction with scratch-resistant, powder-coat finish supports weights of up to 88 lb
- Fits most 13- to 27-inch flat-panel displays
- It comes preassembled for quick and easy installation and features horizontal adjustment to compensate for off-center wall studs
- 5-year warranty
- Green, RoHS-compliant design

Highlights

- **SEE NEW MODEL - DWT1327S**
- Low-profile mounting keeps unit out of sight for sleek, professional appearance
- Fits most flat-panel displays from 13" to 27"
- Tilt adjustment improves viewing angles in applications where the audience is below the display
- Horizontal adjustment compensates for off-center wall studs
- Wide range of motion with -15° to +10° tilt capability
- Supports up to 88 lbs.
- 5-year warranty

Package Includes

- DWT1323S Tilt Flat-Screen Wall Mount
- Mounting Hardware
- Owner's Manual

Specifications

OVERVIEW

Mounting Location

Wall



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

PHYSICAL	
Unit Weight (lbs.)	1.01
Unit Weight (kg)	.45
Color	Black
Monitor Display Size (in.)	13 - 27
Monitor Display Size (cm)	33.02 - 68.58
VESA Pattern (mm)	75x75; 100x100
Motion	Tilt
Degrees of Motion	-15/+10 Tilt;
Min/Max Arm Extension (in.)	N/A
Min/Max Arm Extension (cm)	N/A
Maximum Weight Capacity (lbs.)	88
Maximum Weight Capacity (kg)	39
FEATURES & SPECIFICATIONS	
Tools Necessary	Yes
Cord Management	No
WARRANTY	
Product Warranty Period (U.S. & Canada)	5-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.