

## Mini DisplayPort to VGA Adapter, Video Converter for Mac/PC, 1920x1200/1080p (M/F), 6-in.

MODEL NUMBER: **P137-06N-VGA**



### Description

Tripp Lite's P137-06N-VGA Mini-Displayport to VGA Adapter allows you to connect a Mac or PC with a Mini-Displayport output to a VGA monitor. Compatible with the Thunderbolt port on Mac computers. Supports computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p. Fully-molded ends ensure long life enjoyment. It features a simple plug and play design with an integrated chip that converts the digital Mini-Displayport signal to analog VGA; no drivers or setup needed. Simply plug the adapter into your Mini-Displayport source and connect your VGA cable between it and your monitor.

### Features

- Connect a VGA monitor to a Mac or PC with a Mini Displayport output
- Compatible with the Thunderbolt port on Mac computers
- Plug-and-play convenience—no drivers or software needed
- Supports computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p

## Specifications

OVERVIEW	
Chromebook Compatible	No
Display Style	Adapter
Model Type	VGA
Cable Types	DISPLAYPORT
INPUT	
Cable Length (ft.)	0.5

### Highlights

- Connect a VGA monitor to a Mac or PC with a Mini Displayport output
- Compatible with the Thunderbolt port on Mac computers
- Plug-and-play convenience—no drivers or software needed
- Supports computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p

### System Requirements

- Mac or PC with a Mini Displayport port; Compatible with the Thunderbolt port on Mac computers
- Monitor with a VGA port

### Package Includes

- Mini-DisplayPort to VGA Adapter



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Cable Length (m)	0.15
Cable Length (in.)	6
<b>PHYSICAL</b>	
Color	White
<b>CONNECTIONS</b>	
Connector A	MINI DISPLAYPORT (MALE)
Connector B	HD15 (FEMALE) & 3.5MM (FEMALE)
<b>CERTIFICATIONS</b>	
Certifications	RoHS
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.