

Cat5e 350MHz Molded Patch Cable (RJ45 M/M) - Yellow, 6-ft.

MODEL NUMBER: N002-006-YW



Description

Tripp Lite's 6-ft. yellow category 5e (Cat5e) patch cable has 2 standard RJ45 molded male connectors featuring integral strain relief. The cable is manufactured from PVC 4-pair stranded UTP and is rated for 350MHz/1Gbps communication. All cables are offered in a variety of lengths and colors for all category 5 (Cat5) and 5e cabling needs. Snagless category 5e patch cables are also available (N001-Series).

Features

- Cabling for category 5 (Cat5) and 5e (Cat5e) applications
- Length: 6-ft. Color: yellow Connectors: RJ45 male
- · Feature molded connectors with integral strain relief
- PVC 4-pair stranded UTP
- Rated for 350MHz/ 1Gbps communication
- Meets most current industry standards including IEEE 802.3ab, IEEE 802.5, ANSI/EIA/TIA 568, ISO/IEC 11801 and ETL (category 5e draft 11)
- Available in other colors and lengths
- Also available in a snagless design (N001-Series) to protect the locking tabs on the RJ45 connectors from being damaged or snapped off during
 installation
- Also available Cat6 cables (N201-Series)

Specifications

OVERVIEW	
Style	Cat5/5e
Model Type	Molded
Cable Types	CAT5/CAT5E

Highlights

- Premium cabling for Category 5 and 5e applications—rated for 350 MHz/1 Gbps communications
- IEEE 802.3ab
- PVC 4-pair stranded UTP
- All cables feature boots with integral strain-relief and RJ45 (Male) connectors

System Requirements

For 1000Base-T (1Gbps
 Ethernet), 10/100Base-T
 (Ethernet), 100 Mbps TPDDI,
 155 Mbps ATM, ISDN, voice and
 Token Ring Type3 applications

Package Includes

 6-ft. Cat5e Yellow Patch Cable Molded 350MHz



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

INPUT		
Cable Length (ft.)	6	
Cable Length (m)	1.83	
PHYSICAL		
Color	Yellow	
CONNECTIONS		
Connector A	RJ45 (MALE)	
Connector B	RJ45 (MALE)	
CERTIFICATIONS		
Certifications	RoHS-Compliant	
WARRANTY		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.