

UPS Replacement Battery Cartridge for Tripp Lite, APC, Belkin, Best, Powerware, Liebert & other UPS

MODEL NUMBER: **RBC51**



Description

Tripp Lite's RBC51 premium UPS replacement battery cartridge breathes new life into UPS systems suffering from expired or weak internal batteries. Like every Tripp Lite battery cartridge, it is carefully screened and certified to meet or exceed original manufacturer specifications and ships ready for installation in your UPS system. Its reusable packaging holds expired batteries for recycling center delivery. The RBC51 is compatible with a wide variety of UPS systems, including select models from Tripp Lite, APC, Belkin, Best, Powerware, Liebert and more.

Features

- Restores UPS runtime performance to its original runtime specifications
- Reusable packaging contains expired batteries for recycling center delivery
- Compatible with a variety of UPS brands

Specifications

| BATTERY | |
|---------------------------------|---------------------------------------------------------|
| Included Battery Set | Includes 1 12V battery |
| Typical Battery Lifespan | 3 - 5 years, depending on host UPS operating conditions |
| PHYSICAL | |
| Shipping Dimensions (hwd / in.) | 6 x 7.5 x 12 |
| Shipping Dimensions (hwd / cm) | 15.2 x 19.1 x 30.5 |
| Shipping Weight (lbs.) | 7 |
| Shipping Weight (kg) | 3.18 |
| Unit Dimensions (hwd / in.) | 3.6875 x 2.5 x 5.875 |

Highlights

- Up to 30% longer runtime than basic replacements
- OEM certified premium batteries
- Rugged, leakproof construction
- Maintenance-free
- Wide operating temperature range

Applications

- Extends the operating life of older UPS systems
- Restores or enhances runtimes of all UPS systems exhibiting reduced power failure runtime

Package Includes

- RBC51 UPS Replacement Battery Cartridge
- Owner's Manual



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| | |
|-----------------------------------------|---------------------------|
| Unit Dimensions (hwd / cm) | 9.4 x 6.4 x 14.9 |
| ENVIRONMENTAL | |
| Relative Humidity | 0 - 95% non-condensing |
| Operating Elevation (ft.) | 0 - 10,000 |
| Storage Elevation (ft.) | 0 - 50,000 |
| Operating Elevation (m) | 0-3000 m |
| Storage Elevation (m) | 0 - 15,200 m |
| WARRANTY | |
| Product Warranty Period (U.S. & Canada) | 18-month limited warranty |
| Product Warranty Period (International) | 1-year limited warranty |
| Product Warranty Period (Mexico) | 1-year limited warranty |
| Product Warranty Period (Puerto Rico) | 1-year limited warranty |

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.