

## 58U Heavy-Duty 4-Post SmartRack Open Frame Rack - Organize and Secure Network Rack Equipment

MODEL NUMBER: **SR4POST58HD**



### Highlights

- 58U Heavy-Duty 4-post open frame rack
- Black steel with square, numbered mounting holes
- Toolless button holes to accept PDUs or cable managers

### Package Includes

- SR4POST58HD Heavy-Duty 4-Post Open Frame Rack
- Installation hardware
- (2x) PDU/Cable management brackets
- Owner's manual with warranty information

### Description

SmartRack 4-post heavy-duty open frame racks are an economical solution for 19-inch rackmount applications.

### Features

- Weight capacity of 3000 lbs. stationary
- Supports equipment depths up to 35 inches
- Textured, black powder coat finish
- Heavy-duty cold-rolled steel construction
- Numbered mounting positions
- Bolt down provisions
- Self-squaring design
- Easy assembly
- Optional SRCASTERHDKIT heavy-duty caster kit permits mobile use of 3,000 lb rolling loads
- Optional SR58SIDE4PHD side panels for end-of-the-row aesthetics

## Specifications

OVERVIEW	
Style	4-Post
PHYSICAL	
Installed Whole System Maximum Rack Depth (in.)	35.25



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Installed Whole System Maximum Rack Depth (cm)	89.54
Rack Height (U Spaces)	58
Shipping Dimensions (hwd / in.)	6.75 x 9.5 x 111.25
Shipping Dimensions (hwd / cm)	17.15 x 24.13 x 282.58
Shipping Weight (lbs.)	133
Shipping Weight (kg)	59.85
Unit Dimensions (hwd / in.)	107.5 x 24 x 35.25
Unit Weight (lbs.)	125
Unit Weight (kg)	56.25
Unit Dimensions (cm)	273.1 x 60.96 x 89.54
Color	Black
Weight Capacity - Stationary (lbs.)	3000
Weight Capacity - Stationary (kg)	1350
Hinged (Swings Away from Wall Bracket)	No
<b>CERTIFICATIONS</b>	
NOM (Mexico)	Tested to NOM (Mexico)
Approvals	EIA-310-D, IEC 60297-3-100, DIN 41494, RoHS
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.