

## 120V Single Phase Whip in 10 ft. length with L5-30R for Breakered 3 Phase Distribution Cabinets

MODEL NUMBER: **SUWL530C-10**



### Highlights

- 120V single phase whip distribution cabinet accessory
- 10 ft. length with 3 ft. removed outer jacket
- 3 conductor 10 AWG stranded wire
- L5-30R outlet (120V 30A)

### Description

120V single phase whip with L5-30R outlet distributes power from 3 phase distribution cabinet to critical equipment racks. 10 ft. insulated and 3 ft. of removed outer jacket cabling supports hardwire connection to SUBB130 circuit breaker in SUDC208V series distribution racks. L5-30R outlet is compatible with 120V loads and Power Distribution Units (PDUs) supporting a L5-30P plug-in connection.

### Features

- 120V single phase whip with L5-30R outlet
- Distributes power from 3 phase distribution cabinet to critical equipment racks
- 10 ft. insulated and 3 ft. of removed outer jacket cabling supports hardwire connection to SUBB130 circuit breaker in SUDC208V series distribution racks
- L5-30R outlet is compatible with 120V loads and Power Distribution Units (PDUs) supporting a L5-30P plug-in connection

## Specifications

| OVERVIEW                 |   |
|--------------------------|---|
| Model Type               | Whips   |
| Accessories Type         | Single-Phase Whip Cable   |
| OUTPUT                   |   |
| PDU Recommendation Notes | Compatible with all PDU brands fitted with a L5-30P (30A 120V) input plug, including Tripp Lite <a href="#">PDU2430</a> , <a href="#">PDUMH30</a> , <a href="#">PDUMV30</a> , <a href="#">PDUMNH30</a> , <a href="#">PDUMNV30</a> , <a href="#">PDUMH30NET</a> and <a href="#">PDUMV30NET</a> |
| Outlet Type              | L5-30R (1)  |
| INPUT                    |   |
| Input Connection Type    | Hardwire (3 wire - L, N, G)   |



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

|                                     |                         |
|-------------------------------------|-------------------------|
| Cable Length (ft.)                  | 10                      |
| Cable Length (m)                    | 3.05                    |
| <b>PHYSICAL</b>                     |                         |
| Shipping Weight (lbs.)              | 6                       |
| Shipping Weight (kg)                | 2.7                     |
| Unit Weight (lbs.)                  | 5                       |
| Unit Weight (kg)                    | 2.3                     |
| Color                               | Black                   |
| <b>WARRANTY</b>                     |                         |
| Product Warranty Period (Worldwide) | 1-year limited warranty |

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.