

208/240V Single Phase Whip in 10-ft length with L6-30R for Breakered 3 Phase Distribution Cabinets

MODEL NUMBER: **SUWL630C-10**



Highlights

- 208/240V single phase whip distribution cabinet accessory
- 10 ft. length with 3 ft. removed outer jacket
- 3 conductor 10AWG stranded wire
- L6-30R outlet (208/240V 30A)

Description

208/240V single phase whip with L6-30R outlet distributes power from 3 phase distribution cabinet to critical equipment racks. 10 ft. insulated and 3 ft. of removed outer jacket cabling supports hardwire connection to SUBB230 circuit breaker in SUDC208V series 3 phase distribution racks. L6-30R outlet is compatible with 208/240V loads and Power Distribution Units (PDUs) supporting a L6-30P plug-in connection.

Features

- 208/240V single phase whip with L6-30R outlet
- Distributes power from 3 phase distribution cabinet to critical equipment racks
- 10 ft. insulated and 3 ft. of removed outer jacket cabling supports hardwire connection to SUBB230 circuit breaker in SUDC208V series 3 phase distribution racks
- L6-30R outlet is compatible with 208/240V loads and Power Distribution Units (PDUs) supporting a L6-30P plug-in connection

Specifications

| OVERVIEW | |
|--------------------------|---|
| Model Type | Whips |
| Accessories Type | Single-Phase Whip Cable |
| OUTPUT | |
| PDU Recommendation Notes | Compatible with all PDU brands fitted with a L6-30P (30A 208/240V) input plug, including Tripp Lite PDU1230 , PDUV30HV , PDUMH30HV , PDUHV30HV , PDUMNH30 , PDUMNV30 , PDUMH30HV19NET , PDUMH30HVNET and PDUMV30HVNET |
| Outlet Type | L6-30R (1) |



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| INPUT | |
|-------------------------------------|-----------------------------|
| Input Connection Type | Hardwire (3 wire - L, N, G) |
| Cable Length (ft.) | 10 |
| Cable Length (m) | 3.05 |
| PHYSICAL | |
| Shipping Weight (lbs.) | 5.6 |
| Shipping Weight (kg) | 2.5 |
| Color | Black |
| WARRANTY | |
| Product Warranty Period (Worldwide) | 1-year limited warranty |

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.