

Protect It! 230V Surge Protector with 2 French/Belgian Outlets, 0.33M Cord, 380 Joules, French plug

MODEL NUMBER: **TLP2USBF**



Highlights

- 2 safety outlets
- 380 joule rating
- 2 USB ports
- 33 cm cord

Applications

Ideal for notebooks, home computers, printers, scanners, and desk lamps.

Package Includes

- TLP2USBF surge suppressor
- Instruction manual and warranty information

Description

Tripp Lite's Protect It!™ TLP2USBF offers economical AC surge suppression for full protection of 220-250V home computers, printers, scanners, and desk lamps. The TLP2USBF offers 2 French Type E outlets and 33 cm AC line cord. 2 USB ports are perfect for charging cell phones, iPods, MP3 players and other mobile devices. Internal safety covers protect against accidental contact with unused outlets.

Features

- Protect It!™ TLP2USBF offers economical AC surge suppression
- 380 joules AC surge suppression shields equipment from surges and line noise
- 2 French type E outlets protect computers and peripherals
- 2 USB ports are perfect for charging cell phones, iPods, MP3 players and other mobile devices
- 33 cm cord with French plug
- Internal safety covers protect against accidental contact with unused outlets

Specifications

OVERVIEW	
Style	Strip
OUTPUT	
Output Receptacles	(2) French/Belgian
Circuit Breaker (amps)	10
Transformer Accommodation	1



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

USB Charging	No
INPUT	
Nominal Input Voltage(s) Supported	230V AC
Recommended Electrical Service	230V (220-250V)
Input Connection Type	French
Input Cord Length (ft.)	1
Input Cord Length (m)	0.33
Voltage Compatibility (VAC)	220-250
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	380
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
PHYSICAL	
Shipping Dimensions (hwd / in.)	8.67 x 6.10 x 3.15
Shipping Dimensions (hwd / cm)	22.02 x 15.49 x 8.00
Shipping Weight (lbs.)	.50
Shipping Weight (kg)	0.23
Unit Dimensions (hwd / in.)	5.9 x 2.17 x 1.63
Unit Dimensions (hwd / cm)	14.99 x 5.51 x 4.14
Unit Weight (lbs.)	.48
Unit Weight (kg)	0.22
Housing Color	Black
Receptacle Color	Black
Color (AC Line Cord)	Black
CONNECTIONS	
Ports	2
SPECIAL FEATURES	
Right-Angle Plug	Yes



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.