

## USB 2.0 Hi-Speed A/B Cable with Ferrite Chokes (M/M), 3-ft.

MODEL NUMBER: **U023-003**



### Description

Tripp Lite's 3-ft. gold USB2.0 A/B device cable meets or exceeds USB 2.0 specifications. Connects a USB device to a USB port on a computer or hub. Molded in Ferrite Chokes add additional shielding properties for noisy environments. Backward compatible - can be used with older USB1.1 applications as well. All Tripp Lite USB 2.0 cabling include superior foil shielding for reliable, error-free data communications. The significantly faster data transfer rates of USB 2.0 (up to 480 Mbps) make them perfect for multimedia applications. Features gold plated connectors and gold plated copper contacts for superior conductivity. The cable is manufactured with molded connectors and integral strain relief for extra durability and long life.

### Features

- USB 2.0 certified
- Supports faster data transfer rate (1.5 to 480 Mbps) for low speed and high speed devices including multimedia applications
- Premium double-shielded cables with tinned copper braid and aluminum Mylar foil, Ferrite chokes
- Gold plated connectors and gold plated copper contacts for superior conductivity.
- Molded connectors and integral strain relief for extra durability and long life.

## Specifications

OVERVIEW	
Chromebook Compatible	Yes
Style	USB
Cable Types	USB
OUTPUT	

### Highlights

- Meets or Exceeds USB 2.0 Specifications
- Supports faster data transfer rate (1.5 to 480 Mbps) for low speed and high speed devices, including multimedia applications
- Premium double-shielded cables with tinned copper braid and aluminum mylar foil and Ferrite chokes, feature twisted 28AWG data lines, and 24AWG power lines.
- Gold plated connectors provide superior conductivity

### System Requirements

- Any USB device requiring a USB cable with extra shielding capabilities
- USB2.0 performance only when used with USB2.0 device and USB2.0 controller

### Package Includes

- 3 ft. USB 2.0 Gold Cable USB-A to USB-B with Ferrite Chokes



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

USB Charging	No
<b>INPUT</b>	
Cable Length (ft.)	3
Cable Length (m)	0.9
<b>PHYSICAL</b>	
Color	Black
<b>CONNECTIONS</b>	
Connector A	USB A (MALE)
Connector B	USB B (MALE)
<b>CERTIFICATIONS</b>	
Certifications	RoHS Compliant
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.